



Product: [89503](#)

RS232, #24-3pr, FEP, O/A Foil, FEP Jkt, CMP

Product Description

Computer EIA RS-232 Cable, 24 AWG stranded (7x32) tinned copper conductors, FEP insulation, twisted pair, overall Beldfoil® shield (100% coverage), 24 AWG stranded tinned copper drain wire, FEP jacket, plenum rated

Technical Specifications

Product Overview

Suitable Applications:	extreme high/low temperature environments; rs-232 applications; computer communications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; panel wiring
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
24	7x32	TC - Tinned Copper	3

Conductor Count: 6

Insulation

Material	Nominal Wall Thickness
FEP - Fluorinated Ethylene Propylene	0.006 in

Color Chart

Number	Color
1	Black & White
2	Black & Red
3	Black & Green

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	24	7x32

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
FEP - Fluorinated Ethylene Propylene	0.175 in	0.014 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
24.1 Ohm/1000ft	15.9 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
21 pF/ft	40 pF/ft

Inductance

Nominal Inductance

0.17 µH/ft

Current

Max. Recommended Current [A]

1.5 Amps per Conductor at 25°C

Voltage

UL Voltage Rating

300 V RMS

Temperature Range

Operating Temp Range: -70°C To +200°C

Mechanical Characteristics

Bulk Cable Weight: 21 lbs/1000ft

Max. Pull Tension: 39 lbs

Min Bend Radius/Minor Axis: 1.75 in

Standards

NEC/(UL) Compliance: CMP

CEC/C(UL) Compliance: CMP

CPR Euroclass: Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2003/96/EC (BFR): Yes

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2012/19/EU (WEEE): Yes

EU Directive Compliance: EU Directive 2003/11/EC (BFR)

EU CE Mark: Yes

EU RoHS Compliance Date (yyyy-mm-dd): 2005-04-01

MII Order #39 (China RoHS): Yes

Flammability, LSOH, Toxicity Testing

C(UL) Flammability: FT1

UL Flammability: NFPA 262 Plenum Flame Test (UL910)

CSA Flammability: FT6

IEC Flammability: IEC 60332-1-2

UL voltage rating: 300 V RMS

Plenum/Non-Plenum

Plenum (Y/N): Yes

Part Number

Non-Plenum Number: 9503

Variants

Item #	Color	UPC
89503 002100	Red	612825220992
89503 0021000	Red	612825221005
89503 002500	Red	612825221012

Footnote: C - CRATE REEL PUT-UP.

History

Update and Revision: Revision Number: 0.235 Revision Date: 09-30-2020

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.