



**Product:** [89901](#)

Transceiver 10BASE5, #20-4pr, FEP, Individ. Foil Shielded pairs with Isolated Overall Duofoil + Brd, CMP

## Product Description

IEEE 802.3 Ethernet Transceiver 10BASE5, 20 AWG stranded (7x28) tinned copper conductors, plenum, FEP insulation, twisted pairs, Individually foil shielded pairs, overall polyester isolation tape + Duofoil® + tinned copper braid shield (95% coverage), drain wire, light gray fluorocopolymer (PVDF) jacket, plenum rated

## Technical Specifications

### Product Overview

Suitable Applications:	10Base5 Transceiver
------------------------	---------------------

### Construction Details

#### Conductor

Element	No. of Elements	Size	Stranding	Material
Data Pair(s)	3	20 AWG	7x28	TC - Tinned Copper
Power Pair(s)	1	20 AWG	7x28	TC - Tinned Copper

#### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Data Pair(s)	FEP - Fluorinated Ethylene Propylene (Foam)	0.019 in (0.48 mm)	0.076 in (1.9 mm)	Gray & White, Yellow & Orange, Blue & Green
Power Pair(s)	FEP - Fluorinated Ethylene Propylene	0.011 in (0.28 mm)	0.060 in (1.5 mm)	Black & Red

#### Inner Shield

Element	Shield Type	Material	Coverage	Notes
Data Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	Foil Out
Power Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	Foil Out

#### Outer Shield

Shield Type	Material	Coverage	Drainwire Type	Notes
Tape	Tri-Laminate (Alum+Poly+Alum)	100%	22 AWG (7x30) TC	Polyester Isolating tape under DuoFoil
Braid	Tinned Copper (TC)	93%		

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVDF - Polyvinylidene Fluoride	0.016 in (0.41 mm)	0.370 in (9.40 mm)

Overall Cable Diameter (Nominal): 0.370 in (9.40 mm)

### Electrical Characteristics

#### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Data Pair(s)	11.3 Ohm/1000ft	16.7 pF/ft (54.8 pF/m)	29.5 pF/ft (96.8 pF/m)	78 Ohm	78%	3.8 Amps per Conductor at 25°C
Pair(s)						3.8 Amps per Conductor at 25°C

#### Voltage

<b>UL Voltage Rating</b>
300 V (CMG)

## Mechanical Characteristics

### Temperature

UL Temperature	Operating
150°C	-20°C to +150°C

### Bend Radius

Stationary Min.	Installation Min.
3.7 in (94 mm)	3.7 in (94 mm)

Max. Pull Tension:	97.7 lbs (44.3 kg)
Bulk Cable Weight:	93 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	NFPA 262 (UL910), FT6, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
IEEE Compliance:	IEEE 802.3 10Base5
European Directive Compliance:	EU CE Mark, REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	DEC Part No. 17-01319-00
Non-Plenum Number:	9901

## History

Update and Revision:	Revision Number: 0.500 Revision Date: 12-22-2023
----------------------	--

## Part Numbers

### Variants

Item #	Color	UPC	Footnote
89901 E4X1000	Gray, Light Dec	612825221401	C
89901 E4X500	Gray, Light Dec	612825221418	C

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.