



**Product:** [9306](#)

Audio, Control & Instrument, #22-6pr, PVC, O/A Foil, PVC Jkt, CMG

### Product Description

Audio, Control & Instrument Cable, 22 AWG solid tinned copper conductors, PVC insulation, twisted pairs, overall Beldfoil® shield (100% coverage), 22 AWG stranded tinned copper drain wire, PVC jacket.

### Technical Specifications

#### Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	No. of Pairs
22	Solid	TC - Tinned Copper	6

Conductor Count:	12
------------------	----

##### Insulation

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.013 in

##### Color Chart

Number	Color
1	Black & Red
2	Black & White
3	Black & Green
4	Black & Blue
5	Black & Yellow
6	Black & Brown

##### Color Chart 2

Number
11

##### Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	22	7x30

##### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.315 in	0.032 in

#### Electrical Characteristics

##### Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
16.5 Ohm/1000ft	12.5 Ohm/1000ft

## Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Shield
35 pF/ft	50 pF/ft

## Inductance

Nominal Inductance
0.2 µH/ft

## Current

Max. Recommended Current [A]
2.04 Amps per Conductor at 25°C

## Voltage

UL Voltage Rating
300 V RMS

## Temperature Range

UL Temp Rating:	80°C (UL AWM Style 2464)
Operating Temp Range:	-20°C To +80°C

## Mechanical Characteristics

Bulk Cable Weight:	57 lbs/1000ft
Max. Pull Tension:	102 lbs
Min Bend Radius/Minor Axis:	3.25 in

## Standards

NEC/(UL) Compliance:	CMG
CEC/C(UL) Compliance:	CMG
UL AWM Style Compliance:	2464 (300 V 80°C)
CPR Euroclass:	Eca

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
MII Order #39 (China RoHS):	Yes

## Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading
CSA Flammability:	FT4
IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	Putup Type	Length	UPC
9306 060500	Chrome	Reel	500 ft	612825227465
9306 0601000	Chrome	Reel	1,000 ft	612825227458

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

## History

Update and Revision:	Revision Number: 0.236 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.