


Product: [9059M](#) 



CATV Video, RG6, 18 AWG BCCS, Tri Shield, Messenger

Product Description

18 AWG Solid .040" bare copper-covered steel conductor, gas-injected foam Polyethylene insulation, Duobond Plus® and 75% Aluminum braid shield, PVC jacket with messenger.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
18	Solid	BCCS - Bare Copper Covered Steel	0.04 in	1

Conductor Count:	1
------------------	---

Insulation

Material	Nominal Diameter
PE - Polyethylene (Foam)	0.18 in

Table Notes:	Gas Injected
--------------	--------------

Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
Braid	2	Aluminum		75%
Tape	3	Bi-Laminate (Alum+Poly)		100%

Table Notes:	Tape has shorting fold and is bonded to jacket
--------------	--

Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.275 x 0.416 in

Construction and Dimensions

OuterJacket1, Messenger Diameter:	0.051 in
OuterJacket1, Messenger Material:	Galvanized Steel

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR	Outer Conductor DCR
28 Ohm/1000ft	5.6 Ohm/1000ft	5.6 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
16.2 pF/ft

Inductance

Nominal Inductance
0.097 µH/ft

Impedance

Nominal Characteristic Impedance

75 Ohm

Return Loss (RL)

Frequency [MHz] | Min. Structural Return Loss (SRL)

5-1000 MHz | 20 dB

Delay

Nominal Delay | Nominal Velocity of Propagation (VP) [%]

1.2 ns/ft | 83%

High Freq

Frequency [MHz] | Max. Insertion Loss (Attenuation)

5 MHz | 0.58 dB/100ft

55 MHz | 1.60 dB/100ft

211 MHz | 3.05 dB/100ft

270 MHz | 3.37 dB/100ft

300 MHz | 3.55 dB/100ft

350 MHz | 3.85 dB/100ft

400 MHz | 4.15 dB/100ft

450 MHz | 4.40 dB/100ft

550 MHz | 4.90 dB/100ft

750 MHz | 5.65 dB/100ft

870 MHz | 6.11 dB/100ft

1000 MHz | 6.55 dB/100ft

Voltage

Non-UL Voltage Rating

350 V RMS

Temperature Range

Operating Temp Range: -40°C To +80°C

Mechanical Characteristics

Bulk Cable Weight: 42 lbs/1000ft

Max. Pull Tension: 110 lbs

Min Bend Radius/Minor Axis: 3 in

Standards

RG Type: 6/U Type

Series Type: 6

Applicable Environmental and Other Programs

Environmental Space: Outdoor

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2003/96/EC (BFR): Yes

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2012/19/EU (WEEE): Yes

EU Directive 2015/863/EU: Yes

EU Directive Compliance: EU Directive 2003/11/EC (BFR)

EU RoHS Compliance Date (yyyy-mm-dd): 2004-01-01

MII Order #39 (China RoHS): Yes

Suitability

Suitability - Aerial: Yes

Suitability - Indoor: Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
9059M 0101000	Black	Reel	1,000 ft	612825224143

History

Update and Revision:	Revision Number: 0.329 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.