

**Product:** [9155](#) 

Audio & Instrumentation, 1pr 20 AWG Shielded, 2c 18 AWG, TC, CM



REPRESENTATIVE IMAGE

## Product Description

1 Pair 20 AWG stranded (7x28), Beldfoil® shield; 2 conductors 18 AWG stranded (19x30) TC conductors, polyethylene insulation, 22 AWG stranded TC drain wire, CM PVC jacket.

## Technical Specifications

### Product Overview

Suitable Applications:	Low Voltage Analog Signals (4-20ma, 0-10v, ...); Low Voltage Digital Control (24v, ...); Line Level Audio; Computer Communication; Panel Wiring
------------------------	---

### Construction Details

#### Conductor

Element	Number of Element	Size	Stranding	Material
Pair(s)	1	20 AWG	7x28	TC - Tinned Copper
Conductor(s)	2	18 AWG	19x30	TC - Tinned Copper

#### Insulation

Element	Material	Nom. Thickness	Color Code
Pair(s)	PE - Polyethylene	0.021 in (0.53 mm)	Black & Red
Conductor(s)	PE - Polyethylene	0.021 in (0.53 mm)	Green, White

#### Inner Shield

Element	Shield Type	Material	Coverage	Drainwire Type
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC
Conductor(s)	No Shield			

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.031 in (0.79 mm)	0.262 in (6.65 mm)

Overall Cable Diameter (Nominal): 0.262 in (6.65 mm)

### Electrical Characteristics

#### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Nom. Velocity of Prop.	Max. Current
Pair(s)	10.5 Ohm/1000ft (34.4 Ohm/km)	24 pF/ft (79 pF/m)	46 pF/ft (150 pF/m)	66 Ohm	66%	7 Amps per Conductor at 25°C (20 AWG); 9 Amps per Conductor at 25°C (18 AWG)
Conductor(s)	6.6 Ohm/1000ft (22 Ohm/km)	22 pF/ft (72 pF/m)			66%	9 Amps per conductor @ 25°C

#### Voltage

UL Voltage Rating
300 V (CM, UL AWM 2094)

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating

60°C (UL AWM 2094) -20°C to +60°C

#### Bend Radius

Stationary Min.	Installation Min.
2.6 in (66 mm)	2.6 in (66 mm)

Max. Pull Tension:	69.6 lbs (31.6 kg)
Bulk Cable Weight:	45 lbs/1000ft (67 kg/km)

#### Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum)
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL1685 UL Loading, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CM
AWM Compliance:	AWM 2094
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

#### History

Update and Revision:	Revision Number: 0.353 Revision Date: 04-08-2022
----------------------	--

#### Part Numbers

##### Variants

Item #	Color	Putup Type	Length	UPC
9155 290500	Beige, Light	Reel	500 ft	612825224846
9155 2901000	Beige, Light	Reel	1,000 ft	612825224839
9155 290U1000	Beige, Light	UnReel	1,000 ft	612825388142
9155 2905000	Beige, Light	Reel	5,000 ft	612825224815

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.