



REPRESENTATIVE IMAGE

**Product:** [9156](#)

Electronic, 2 Pr #18 Str TC, PVC Ins, PVC Jkt, CMG

[Request Sample](#)

## Product Description

Electronic, 2 Pair 18AWG (16x30) Tinned Copper, PVC Insulation, PVC Outer Jacket, CMG

## Technical Specifications

### Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

### Construction Details

#### Conductor

Element	Number of Element	Size	Stranding	Material
Pair(s)	2	18 AWG	16x30	TC - Tinned Copper

#### Insulation

Element	Material	Nom. Thickness	Color Code
Pair(s)	PVC - Polyvinyl Chloride	0.013 in (0.33 mm)	Black & Red, Black & White

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.035 in (0.89 mm)	0.333 in (8.46 mm)

Cable Diameter (Nominal):	0.333 in (8.46 mm)
---------------------------	--------------------

### Electrical Characteristics

#### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Pair(s)	5.86 Ohm/1000ft (19.2 Ohm/km)	25.5 pF/ft (83.7 pF/m)	3.9 Amps per Conductor at 20°C

#### Voltage

UL Voltage Rating
300 V (CMG), 300 V (UL AWM 2464)

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating
80°C (UL AWM 2464)	-20°C to +80°C

#### Bend Radius

Stationary Min.	Installation Min.
3.3 in (84 mm)	3.3 in (84 mm)

Max. Pull Tension:	90 lbs (41 kg)
Bulk Cable Weight:	48 lbs/1000ft (71 kg/km)

### Standards and Compliance

Environmental Suitability:	Indoor
Sustainability:	CA Prop 65
Flammability / Fire Resistance:	UL1685 FT4 Loading, FT4, IEC 60332-1-2
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	2464
CEC / C(UL) Compliance:	CMG
CPR Euroclass:	Eca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.353 Revision Date: 10-13-2021
----------------------	--

## Variants

Item #	Color	Putup Type	Length	UPC
9156 060500	Chrome	Reel	500 ft	612825224884
9156 060U500	Chrome	UnReel	500 ft	612825224860
9156 0601000	Chrome	Reel	1,000 ft	612825224877
9156 060U1000	Chrome	UnReel	1,000 ft	612825224853
9156 0605000	Chrome	Reel	5,000 ft	612825224891

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.