



Product: [9396](#)

Microphone Cable, 1 Conductor 25 AWG, TC



Product Description

25 AWG stranded (7x33) composite copper conductor, PVC insulation, (3) strands TC, (4) strands TCCS, TC spiral shield (90% coverage), PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor				
AWG	Stranding	Material	Nominal Diameter	No. of Coax
25	3x33	TC - Tinned Copper (High Conductivity)	0.021 in	1
Conductor Count:			1	

Insulation	
Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.058 in

Outer Shield		
Type	Material	Coverage [%]
Spiral Serve / Screen	Tinned Copper (TC)	90%

Outer Jacket	
Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.1 in

Electrical Characteristics

Conductor DCR			
Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
46 Ohm/1000ft	46 Ohm/1000ft	17 Ohm/1000ft	17 Ohm/1000ft

Capacitance	
Max. Capacitance Conductor to Shield	Nom. Capacitance Conductor to Shield
75 pF/ft	75 pF/ft

Impedance	
Nominal Characteristic Impedance	
31 Ohm	

Current	
Max. Recommended Current [A]	
1.9 Amps per Conductor at 25°C (10°C Temperature Rise)	

Voltage	
Non-UL Voltage Rating	
300 V DC	

Temperature Range

Non-UL Temp Rating:	60°C
Operating Temperature Range:	-20°C To +60°C

Mechanical Characteristics

Bulk Cable Weight:	7 lbs/1000ft
Max. Pull Tension:	12 lbs
Min. Bend Radius/Minor Axis:	1 in

Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
9396 U90250	Gray, Matte	Reel	250 ft	612825239925

History

Update and Revision:	Revision Number: 0.360 Revision Date: 04-29-2024
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.