

Product: [9204](#) 

MIL-C-17G, RG59, 75 Ohm Coax, #23 Solid BCCS, 95% BC Braid, CMH



Product Description

23 awg solid .023" bare copper-covered steel conductor, polyethylene insulation, bare copper braid shield (95% coverage), non-contaminating PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
23	Solid	BCCS - Bare Copper Covered Steel	0.023 in	1

Conductor Count:

Insulation

Material	Nominal Diameter
PE - Polyethylene	0.145 in

Outer Shield Material

Type	Material	Coverage [%]
Braid	Bare Copper (BC)	95%

Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride (Non-Contaminating)	0.242 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
47 Ohm/1000ft	47 Ohm/1000ft	2.6 Ohm/1000ft	2.6 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
20.5 pF/ft

Inductance

Nominal Inductance
0.115 µH/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.6 dB/100ft
10 MHz	1.1 dB/100ft

50 MHz	2.4 dB/100ft
100 MHz	3.4 dB/100ft
200 MHz	4.9 dB/100ft
400 MHz	7 dB/100ft
700 MHz	9.7 dB/100ft
900 MHz	11.1 dB/100ft
1000 MHz	12 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.54 ns/ft	66%

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)
400 MHz	9 dB/100ft
1000 MHz	16 dB/100ft

Power Rating

Frequency [MHz]	Max. Power Rating [W]
50 MHz	450 W
100 MHz	300 W
200 MHz	200 W
400 MHz	130 W
700 MHz	95 W
900 MHz	80 W
1,000 MHz	72 W

Voltage

Non-UL Voltage Rating
1700 V RMS

Temperature Range

Non-UL Temp Rating:	85°C
Operating Temp Range:	-40°C To +85°C

Mechanical Characteristics

Bulk Cable Weight:	36 lbs/1000ft
Max. Pull Tension:	78 lbs
Min Bend Radius/Minor Axis:	2.5 in

Standards

NEC/(UL) Compliance:	CMH
CEC/C(UL) Compliance:	CMH
RG Type:	59/U Type
Military Compliance:	MIL-DTL-17, M17/29-RG59, QPL

Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
EU RoHS Compliance Date (yyyy-mm-dd):	2005-10-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

UL Flammability:	VW-1
CSA Flammability:	FT1

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
9204 010500	Black	Reel	500 ft	612825358879
9204 0101000	Black	Reel	1,000 ft	612825225256

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.262 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.