



Product: [9251](#)

52 Ohm, RG8, 13 AWG, CMX



Product Description

RG-8/U type, 13 AWG stranded (7x21) .085" bare copper conductor, polyethylene insulation, bare copper braid shield (95% coverage), non-contaminating PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
13	7x21	BC - Bare Copper	0.085 in	1

Conductor Count: 1

Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PE - Polyethylene	0.285 in	0.285 in

Outer Shield

Type	Material	Coverage [%]
Braid	Bare Copper (BC)	95%

Outer Jacket

Material	Nominal Diameter
PVC - Polyvinyl Chloride (Non-Contaminating)	0.405 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
1.9 Ohm/1000ft	1.9 Ohm/1000ft	1.2 Ohm/1000ft	1.2 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
28.5 pF/ft

Inductance

Nominal Inductance
0.079 μ H/ft

Impedance

Nominal Characteristic Impedance
52 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.2 dB/100ft
10 MHz	0.6 dB/100ft

50 MHz	1.3 dB/100ft
100 MHz	1.9 dB/100ft
200 MHz	2.8 dB/100ft
400 MHz	4.2 dB/100ft
700 MHz	5.9 dB/100ft
900 MHz	6.9 dB/100ft
1000 MHz	7.4 dB/100ft
4000 MHz	23.2 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.54 ns/ft	66%

Voltage

Non-UL Voltage Rating	UL Voltage Rating
3700 V RMS	150 V RMS
	30 V RMS (UL AWM Style 1354)

Temperature Range

UL Temp Rating:	60°C
Operating Temperature Range:	-40°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	105 lbs/1000ft
Max. Pull Tension:	190 lbs
Min. Bend Radius/Minor Axis:	4 in

Standards

NEC/(UL) Compliance:	CMX
CEC/C(UL) Compliance:	CMX
UL AWM Style Compliance:	AWM 1354 (30 V 60°C)
RG Type:	8

Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	VW-1
UL voltage rating:	150 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
--------	-------	-------------	--------	-----

9251 010500	Black	Reel	500 ft	612825225782
9251 0101000	Black	Reel	1,000 ft	612825225775

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.384 Revision Date: 11-09-2022
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.