



**Product:** [9258](#)

50 Ohm Wireless Transmission Coax, RG-8, 16 AWG Str BC, 95% BC Braid, PVC Jkt, CM

### Product Description

50 Ohm Wireless Transmission Coax, RG-8X, 16 AWG (19x29) Bare Copper Conductor , PE Insulation, 95% Bare Copper Braid Shield, PVC Jacket, CM

### Technical Specifications

#### Product Overview

Suitable Applications:	Point-to-point and point-to-multipoint wireless antenna communication; Wireless microphones, Two-Way Radios, Amateur (Ham) Radio, Low Power FM, GPS, RFID (Radio Frequency Identification)
------------------------	--

#### Construction Details

RG Type:	8X
----------	----

#### Conductor

Size	Stranding	Nom. Diameter	Material
16 AWG	19x29	0.057 in	BC - Bare Copper

#### Insulation

Material	Nom. Insulation Diameter
PE - Polyethylene (Foam)	0.155 in (3.94 mm)

#### Outer Shield

Outer Shield Type	Material	Coverage
Braid	Bare Copper (BC)	95%

#### Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.242 in (6.15 mm)

Overall Cable Diameter (Nominal):	0.242 in
-----------------------------------	----------

#### Electrical Characteristics

##### Attenuation

Frequency	Nom. Attenuation
1 MHz	0.3 dB/100ft
10 MHz	0.9 dB/100ft
50 MHz	2.1 dB/100ft
100 MHz	3.1 dB/100ft
200 MHz	4.5 dB/100ft
400 MHz	6.6 dB/100ft
700 MHz	9.1 dB/100ft
900 MHz	10.7 dB/100ft
1000 MHz	11.2 dB/100ft

##### Power Rating

Frequency	Max. Power Rating
10 MHz	1,000 W

50 MHz	370 W
100 MHz	250 W
200 MHz	190 W
400 MHz	110 W
700 MHz	75 W
1,000 MHz	60 W

#### Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
4.1 Ohm/1000ft (13 Ohm/km)	3.1 Ohm/1000ft (10 Ohm/km)	24.8 pF/ft (81.4 pF/m)	50 Ohm	82%

#### Voltage

UL Voltage Rating
300 V (CM)

## Mechanical Characteristics

#### Temperature

UL Temperature	Operating
60°C (UL AWM 1354)	-30°C to +75°C

#### Bend Radius

Installation Min.
2.4 in

Max. Pull Tension:	61 lbs (28 kg)
Bulk Cable Weight:	36 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Aerial - Black only, When supported by messenger wire
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL1685 UL Loading
NEC / UL Compliance:	CM
AWM Compliance:	AWM 1354
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.344 Revision Date: 04-08-2022
----------------------	--

## Part Numbers

#### Variants

Item #	Color	Putup Type	Length	UPC
9258 010500	Black	Reel	500 ft	612825225805
9258 010U500	Black	UnReel	500 ft	612825358886
9258 0101000	Black	Reel	1,000 ft	612825225836
9258 010U1000	Black	UnReel	1,000 ft	612825225812
9258 0091000	White	Reel	1,000 ft	612825225829

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.