



Product: [9259](#)

75 Ohm Analog Video Coax, RG-59, 22 AWG Str BC, 95% BC Braid, PVC Jkt, CM

Product Description

75 Ohm Analog Video Coax, RG-59, 22 AWG (7x30) Bare Copper Conductor , PE Insulation, 95% Bare Copper Braid Shield, PVC Jacket, CM

Technical Specifications

Product Overview

Suitable Applications:	Standard analog video
------------------------	-----------------------

Construction Details

RG Type:	59
----------	----

Conductor

Size	Stranding	Nom. Diameter	Material
22 AWG	7x30	0.029 in	BC - Bare Copper

Insulation

Material	Nom. Insulation Diameter	Color Code
PE - Polyethylene (Foam)	0.146 in (3.71 mm)	White

Outer Shield

Outer Shield Type	Material	Coverage
Braid	Bare Copper (BC)	95%

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.240 in (6.10 mm)

Overall Cable Diameter (Nominal):	0.240 in (6.10 mm)
-----------------------------------	--------------------

Electrical Characteristics

Attenuation

Frequency	Nom. Attenuation
1 MHz	0.3 dB/100ft
5 MHz	0.65 dB/100ft
10 MHz	0.9 dB/100ft
50 MHz	2.1 dB/100ft
100 MHz	3 dB/100ft
200 MHz	4.5 dB/100ft
400 MHz	6.6 dB/100ft
700 MHz	8.9 dB/100ft
900 MHz	10.1 dB/100ft
1000 MHz	10.9 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
15 Ohm/1000ft	2.6 Ohm/1000ft (8.5 Ohm/km)	17.3 pF/ft (56.8 pF/m)	75 Ohm	78%

Voltage

UL Voltage Rating

300 V (CM), 30 V (UL AWM 1354)

Mechanical Characteristics

Temperature

Operating

-40°C to +80°C

Bend Radius

Installation Min.

2.4 in (61 mm)

Max. Pull Tension:	65 lbs (29 kg)
Bulk Cable Weight:	33 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor, Aerial - Black only, When supported by messenger wire
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL1685 UL Loading
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	CM
AWM Compliance:	AWM 1354
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	89259

History

Update and Revision: Revision Number: 0.490 Revision Date: 04-29-2024

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
9259 010100	Black	Reel	100 ft	612825358893	
9259 010500	Black	Reel	500 ft	612825354987	C
9259 010U500	Black	UnReel	500 ft	612825357841	
9259 0101000	Black	Reel	1,000 ft	612825352969	C
9259 010U1000	Black	UnReel	1,000 ft	612825358770	
9259 0101200	Black	Reel	1,200 ft	612825352921	
9259 0101500	Black	Reel	1,500 ft	612825358787	
9259 0105000	Black	Reel	5,000 ft	612825358909	C

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.