

**Part Number: 9497**

Speaker Cable, 2 Conductor 16 AWG TC, Unshielded, CM



**Product Description**

2 Conductor 16 AWG stranded (19x29) ETP high-conductivity tinned copper conductors, PVC insulation, cabled.

**Technical Specifications**

**Product Overview**

Environmental Space:	Indoor (Not Riser or Plenum)
Suitable Applications:	Speaker Cable

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Conductors
16	19x29	High Conductivity TC - Tinned Copper	2
Conductor Count:		2	
Conductor Size:		16 AWG	

**Insulation**

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.023 in

**Color Chart**

Number	Color
1	Black
2	Orange

**Outer Shield Material**

Material
Unshielded

**Outer Jacket Material**

Material	Nominal Diameter
Unjacketed	0.21 in

**Electrical Characteristics**

**Conductor DCR**

Nominal Conductor DCR
4.27 Ohm/1000ft

**Inductance**

Nominal Inductance
0.19 $\mu$ H/ft

**Current**

Max. Recommended Current [A]

7.1 Amps per conductor @ 25°C

## Voltage

UL Voltage Rating
300 V RMS (UL AWM Style 1007)

## Temperature Range

UL Temp Rating:	80°C (UL AWM Style 1007)
Operating Temp Range:	-30°C To +80°C

## Mechanical Characteristics

Bulk Cable Weight:	28 lbs/1000ft
Max Recommended Pulling Tension:	84 lbs
Min Bend Radius/Minor Axis:	2.25 in

## Standards

UL AWM Style:	UL Style 1007 (300 V 80°C)
CPR Euroclass:	Eca

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Indoor:	Yes
-----------------------	-----

## Flammability, LSOH, Toxicity Testing

UL Flammability:	VW-1
UL voltage rating:	300 V RMS (UL AWM Style 1007)

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	Footnote
9497 0001000	None	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.