



Product: [9363](#)

High Perform Instr, 1 Tri #22 Str TC, PVC Ins E1, OS, PVC Jkt, PLTC

Request Sample

Product Description

High Performance Instrumentation, 1 Triad 22AWG (7x30) Tinned Copper, PVC Insulation E1 Color Code, Overall Beldfoil® Shield, PVC Outer Jacket, PLTC

Technical Specifications

Product Overview

| | |
|------------------------|---|
| Suitable Applications: | Instrumentation, Sensors, Valves, Positioners, RTD, 4-20mA, 0-10V |
|------------------------|---|

Construction Details

Conductor

| Element | Number of Element | Size | Stranding | Material |
|----------|-------------------|--------|-----------|--------------------|
| Triad(s) | 1 | 22 AWG | 7x30 | TC - Tinned Copper |

Insulation

| Element | Material | Nom. Thickness | Nom. Insulation Diameter | Color Code |
|----------|--------------------------|--------------------|--------------------------|---------------------|
| Triad(s) | PVC - Polyvinyl Chloride | 0.017 in (0.43 mm) | 0.062 in (1.6 mm) | Black , White , Red |

Outer Shield

| Shield Type | Material | Coverage | Drainwire Type |
|-------------|-------------------------|----------|------------------|
| Tape | Bi-Laminate (Alum+Poly) | 100% | 22 AWG (7x30) TC |

Outer Jacket

| Material | Nom. Thickness | Nom. Diameter | Ripcord |
|--------------------------|--------------------|--------------------|---------|
| PVC - Polyvinyl Chloride | 0.037 in (0.94 mm) | 0.210 in (5.33 mm) | Yes |

| | |
|-----------------------------------|--------------------|
| Overall Cable Diameter (Nominal): | 0.210 in (5.33 mm) |
|-----------------------------------|--------------------|

Electrical Characteristics

Electricals

| Element | Nom. Conductor DCR | Nom. Capacitance Cond-to-Cond | Nom. Capacitance Cond-to-Shield | Max. Current |
|----------|--------------------|-------------------------------|---------------------------------|--------------------------------|
| Triad(s) | 18.2 Ohm/1000ft | 26 pF/ft (85 pF/m) | 45 pF/ft (150 pF/m) | 2.8 Amps per Conductor at 25°C |

Voltage

| UL Voltage Rating |
|-------------------|
| 300 V (PLTC, CMG) |

Mechanical Characteristics

Temperature

| UL Temperature | Operating |
|----------------|-----------------|
| 105°C | -30°C to +105°C |

| | |
|--------------|----------|
| Table Notes: | AWM 80°C |
|--------------|----------|

Bend Radius

| Stationary Min. | Installation Min. |
|-----------------|-------------------|
| 2.1 in (53 mm) | 2.1 in (53 mm) |

| | |
|--------------------|----------------|
| Max. Pull Tension: | 36 lbs (16 kg) |
| Bulk Cable Weight: | 24 lbs/1000ft |

Standards and Compliance

| | |
|----------------------------------|---|
| Environmental Suitability: | Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance |
| Flammability / Reaction to Fire: | UL 1685 UL Loading, FT4, T-29-520, IEEE 1202 |
| NEC / UL Compliance: | Article 725, Article 727, Article 800, CMG, ITC, PLTC |
| AWM Compliance: | AWM 2464 |
| CEC / C(UL) Compliance: | CMG |
| European Directive Compliance: | EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE) |
| APAC Compliance: | China RoHS II (GB/T 26572-2011) |

History

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.554 Revision Date: 01-20-2023 |
|----------------------|--|

Part Numbers

Variants

| Item # | Color | UPC |
|---------------|--------|--------------|
| 9363 0602500 | Chrome | 612825239406 |
| 9363 0605000 | Chrome | 612825239413 |
| 9363 060U1000 | Chrome | 612825239383 |
| 9363 060U500 | Chrome | 612825239390 |

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.