



Product: [9405](#)

Electronic, 2+6 C #18+16 Str TC, PVC Ins, PVC Jkt, CM

Request Sample

### Product Description

Electronic, 2+6 Conductor 18+16AWG (19x30+19x29) Tinned Copper, PVC Insulation, PVC Outer Jacket, CM

### Technical Specifications

#### Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio; panel wiring
------------------------	---

#### Construction Details

##### Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	6	18 AWG	19x30	TC - Tinned Copper
Conductor(s)	2	16 AWG	19x28	TC - Tinned Copper

##### Insulation

Element	Material	Nom. Thickness	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.019 in (0.48 mm)	Brown, Red, Yellow, Blue, Orange, Green
Conductor(s)	PVC - Polyvinyl Chloride	0.019 in (0.48 mm)	Black, White

##### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.032 in (0.81 mm)	0.345 in (8.76 mm)

Overall Cable Diameter (Nominal):	0.345 in (8.76 mm)
-----------------------------------	--------------------

#### Electrical Characteristics

##### Electricals

Element	Nom. Conductor DCR	Max. Current
Conductor(s)	6.8 Ohm/1000ft (22 Ohm/km)	4 Amps per Conductor at 25°C
Conductor(s)	4.0 Ohm/1000ft (13 Ohm/km)	4.9 Amps per Conductor at 25°C

##### Voltage

UL Voltage Rating
300 V (CM, UL AWM 2464)

#### Mechanical Characteristics

##### Temperature

UL Temperature	Operating
80°C (UL AWM 2464)	-20°C to +80°C

##### Bend Radius

Stationary Min.	Installation Min.
3.5 in (89 mm)	3.5 in (89 mm)

Max. Pull Tension:	181 lbs (82.1 kg)
--------------------	-------------------

Bulk Cable Weight:	87 lbs/1000ft (130 kg/km)
--------------------	---------------------------

## Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, UV Resistance
NEC / UL Compliance:	Article 800, CM
AWM Compliance:	AWM 2464
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.376 Revision Date: 06-01-2023
----------------------	--

## Part Numbers

### Variants

Item #	Color	UPC	Footnote
9405 0601000	Chrome	612825240013	C

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.