



Product: [9581](#)

Electronic, 2 C #14 Sol BC, PVC Ins, OS, Red PVC Jkt, FPLR

[Request Sample](#)

Product Description

Electronic, 2 Conductor 14AWG (Solid) Bare Copper, PVC Insulation, Overall Beldfoil® Shield, Red PVC Outer Jacket, FPLR

Technical Specifications

Product Overview

Suitable Applications:	fire alarms; indoor applications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...)
------------------------	---

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Conductor(s)	2	14	Solid	BC - Bare Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
PVC - Polyvinyl Chloride	0.022 in (0.56 mm)	0.20 in (5.1 mm)	Black, Red

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	16 AWG (19x29) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.042 in (1.1 mm)	0.306 in (7.77 mm)

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
2.62 Ohm/1000ft	55 pF/ft (180 pF/m)	105 pF/ft (344 pF/m)	18 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
105°C	-40°C To +105°C

Bend Radius

Stationary Min.	Installation Min.
4.59 in (117 mm)	4.59 in (117 mm)

Max. Pull Tension:	124 lbs (56.2 kg)
Bulk Cable Weight:	60 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor
Flammability / Reaction to Fire:	UL1666 Riser, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 760, FPLR
AWM Compliance:	AWM 2464
CEC / C(UL) Compliance:	FAS105
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	California State Fire Marshall

Product Notes

Notes:	This cable passes the UL 1685 70,000 BTU Flame Test (comparable to the IEEE 383 Flame Test) and is listed by the California State Fire Marshall. Component Recognized UL 2464, 300V 80°C.
--------	---

History

Update and Revision:	Revision Number: 0.449 Revision Date: 04-08-2022
----------------------	--

Part Numbers

Variants

Item #	Color	UPC
9581 0021000	Red	612825256236
9581 002U500	Red	612825256229

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.