



**Product:** [9729ZH](#)

Electronic, 2 Pr #24 Str TC, PO Ins, OS+TC Brd, LSZH Jkt, CMG

[Request Sample](#)

## Product Description

Electronic, 2 Pair 24AWG (7x32) Tinned Copper, PO Insulation, Overall Beldfoil®+Tinned Copper Braid(65%) Shield, LSZH Outer Jacket, CMG

## Technical Specifications

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Pairs
24	7x32	TC - Tinned Copper	2

Conductor Count:	4
Total Number of Pairs:	2

#### Insulation

Material	Material Trade Name	Nominal Wall Thickness
PE - Polyethylene (Foam)	Datalene®	0.0185 in

#### Color Chart

Number	Color
1	Black and Red
2	Black and White

#### Inner Shield Material

Type	Layer	Material	Coverage [%]	Drainwire Material	Drainwire AWG
Tape	Tape	Bi-Laminate (Alum+Poly)	100%	TC - Tinned Copper	24

#### Outer Jacket Material

Material	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.048 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR
24.0 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
12.5 pF/ft	23.2 pF/ft

#### Inductance

Nominal Inductance
0.23 μH/ft

#### Impedance

Nominal Characteristic Impedance
----------------------------------

100 Ohm

#### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
0.384 MHz	0.74 dB/100ft
0.7056 MHz	0.87 dB/100ft
0.768 MHz	0.88 dB/100ft
1.024 MHz	0.94 dB/100ft
1.4112 MHz	1.01 dB/100ft
1.536 MHz	1.03 dB/100ft
2.048 MHz	1.13 dB/100ft
2.8224 MHz	1.29 dB/100ft
3.072 MHz	1.35 dB/100ft
4.096 MHz	1.57 dB/100ft
5.6448 MHz	1.78 dB/100ft
6.144 MHz	1.84 dB/100ft
8.192 MHz	2.13 dB/100ft
11.2896 MHz	2.45 dB/100ft
12.288 MHz	2.57 dB/100ft
24.576 MHz	3.57 dB/100ft

#### Current

Max. Recommended Current [A]
1 Amp per Conductor at 25°C

#### Voltage

UL Voltage Rating
300 V RMS

#### Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-20°C to 75°C

#### Mechanical Characteristics

Bulk Cable Weight:	36 lbs/1000ft
Max. Pull Tension:	22 lbs
Min Bend Radius/Minor Axis:	3.25 in

#### Standards

NEC Articles:	Article 800
NEC/(UL) Compliance:	CMG
CEC/C(UL) Compliance:	CMG
UL AWM Style Compliance:	21088

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2012-05-08

#### Suitability

Suitability - Indoor:	Yes
-----------------------	-----

#### Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading
UL voltage rating:	300 V RMS

#### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

---

### Variants

Item #	Color	Putup Type	Length	UPC
9729ZH 060500	Chrome	Reel	500 ft	612825382348
9729ZH 0601000	Chrome	Reel	1,000 ft	612825382331

### History

---

Update and Revision:	Revision Number: 0.109 Revision Date: 02-16-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.