



**Product:** [9791](#)

RS232/423 Low Cap, #28-6c, FPO, O/A Foil+Braid, PVC Jkt, CL2

## Product Description

Computer EIA RS-232/423 Cable, 28 AWG stranded (7x36) tinned copper conductors, Datalene® insulation, overall Beldfoil® (100% Coverage) + tinned copper braid shield (65% Coverage), 28 AWG stranded tinned copper drain wire, PVC jacket.

## Technical Specifications

### Product Overview

Suitable Applications:	rs-232 extended distance applications; rs-423 applications; computer communications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; panel wiring
------------------------	--

### Construction Details

#### Conductor

Element	Number of Element	Size	Stranding	Material
Conductor(s)	6	28 AWG	7x36	TC - Tinned Copper

#### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PE - Polyethylene (Foam)	0.015 in (0.38 mm)	0.044 in (1.1 mm)	Black, White, Red, Green, Brown, Blue

#### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	28 AWG (7x36) TC
Braid	Tinned Copper (TC)	65%	

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter	Ripcord
PVC - Polyvinyl Chloride	0.035 in (0.89 mm)	0.225 in	Yes

Overall Cable Diameter (Nominal):	0.225 in
-----------------------------------	----------

### Electrical Characteristics

#### Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
72.8 Ohm/1000ft	12 pF/ft (39 pF/m)	22 pF/ft (72 pF/m)	100 Ohm	78%	2.1 Amps per Conductor at 25°C

#### Voltage

UL Voltage Rating
300 V (CL2), 30 V AC (UL AWM 2919)

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating
80°C	-30°C To +80°C

#### Bend Radius

Stationary Min.	Installation Min.
2.25 in (57.2 mm)	2.25 in

Max. Pull Tension:	14.7 lbs (6.67 kg)
Bulk Cable Weight:	26 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL 1685 UL Loading
NEC / UL Compliance:	Article 725, CL2
AWM Compliance:	AWM 2919
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## Product Notes

Notes:	Datalene® insulation features include a low dielectric constant and a low dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.
--------	--

## History

Update and Revision:	Revision Number: 0.398 Revision Date: 04-08-2022
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC
9791 060500	Chrome	Reel	500 ft	612825258674
9791 0601000	Chrome	Reel	1,000 ft	612825258667

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.