



**Part Number: 9841**

RS485, 1 Pr #24 Str TC, PO Ins, OS+TC Brd, PVC Jkt, CM

[Request Sample](#)

**Product Description**

RS-485, 1 Pair 24AWG (7x32) Tinned Copper, PO Insulation, Overall Beldfoil®+Tinned Copper Braid(90%) Shield, PVC Outer Jacket, CM

**Technical Specifications**

**Product Overview**

Suitable Applications:	RS-485, DMX-512
------------------------	-----------------

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Pairs
24	7x32	TC - Tinned Copper	1

Conductor Count:	2
Total Number of Pairs:	1

**Insulation**

Material	Nominal Wall Thickness
PE - Polyethylene	0.0225 in

**Color Chart**

Color
White/Blue & Blue/White

**Outer Shield Material**

Type	Layer	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	1	Aluminum/Polyester	Beldfoil® with shorting fold	100 %	TC - Tinned Copper	24	7x32 mm
Braid	2	TC - Tinned Copper		90 %			

**Outer Jacket Material**

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.232 in	0.035 in

**Construction and Dimensions**

**Cabling**

Lay Direction	Twists	Filler
Left Hand	4.8 twist/ft	Fibrous Polypropylene

**Electrical Characteristics**

**Conductor DCR**

Nominal Conductor DCR	Nominal Outer Shield DCR
24 Ohm/1000ft	3.4 Ohm/1000ft

**Capacitance**

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield

12.8 pF/ft	23 pF/ft
------------	----------

#### Impedance

Nominal Characteristic Impedance
120 Ohm

#### High Frequency (Nominal/Typical)

Nom. Insertion Loss
0.6 dB/100ft

#### Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.6 ns/ft	66 %

#### Current

Element	Max. Recommended Current [A]
10C Temperature Rise	Per conductor @ 25°C Ambient (10C temperature rise): 2.1 A

#### Voltage

UL Description	UL Voltage Rating
Type CM	300 V RMS (UL type CM)
AWM 2919	30 V RMS (UL AWM 2919)

Electrical Characteristics Notes:	Attenuation @ 1 MHz: .6 dB/100 ft nominal
-----------------------------------	-------------------------------------------

#### Temperature Range

UL Temp Rating:	80°C (UL AWM Style 2919)
Operating Temp Range:	-30°C To +80°C

#### Mechanical Characteristics

Bulk Cable Weight:	36 lbs/1000ft
Max Recommended Pulling Tension:	72.3 lbs
Min Bend Radius/Minor Axis:	2.5 in

#### Standards

NEC Articles:	800
NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
UL AWM Style:	2919 (30 V 80°C)
CPR Euroclass:	Eca

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### Suitability

Suitability - Hazardous Locations:	Yes
Suitability - Indoor:	Yes

#### Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 (UL Loading)
CSA Flammability:	FT1
ISO/IEC Flammability:	IEC 60332-1-2

UL voltage rating:	300 V RMS (CM)
--------------------	----------------

## Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	82841, 89841

## Part Number

### Variants

Item #	Color	UPC	Length	Footnote
9841.0030	Chrome		30 m	
9841.011000	Chrome		1,000 m	
9841.011152	Chrome		152 m	
9841.0111525	Chrome		1,525 m	
9841.012000	Chrome		2,000 m	
9841.01305	Chrome		305 m	
9841.019999	Chrome		151 m	
9841 060100	Chrome	612825259442	100 ft	
9841 0601000	Chrome	612825259459	1,000 ft	C
9841 06010000	Chrome	612825259466	10,000 ft	C
9841 060500	Chrome	612825259473	500 ft	C
9841 0605000	Chrome	612825259480	5,000 ft	
9841.K1305	Chrome		305 m	
9841.031000	Violet		1,000 m	
9841.03305	Violet		305 m	
9841.02305	Yellow		305 m	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

## History

Update and Revision:	Revision Number: 0.311 Revision Date: 08-22-2019
----------------------	--------------------------------------------------

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.