



REPRESENTATIVE IMAGE

Product: [9842LW](#)

RS485, 2 Pr #24 Str TC, PO Ins, OS+TC Brd, LSZH Jkt, Cca

Product Description

RS-485, 2 Pair 24AWG (7x32) Tinned Copper, PO Insulation, Overall Beldfoil®+Tinned Copper Braid(90%) Shield, LSZH Outer Jacket, CPR Cca

Technical Specifications

Product Overview

Suitable Applications:	RS-485, POS; Computer communications; Low Voltage Analog Signals (4-20ma, 0-10v, ...); Low Voltage Digital Control (24v, ...); Line Level Audio; Panel Wiring; serial communication (RS-485 standard) comprising of PLCs, VFDs, HMIs, motors, RTU, SCADA, etc. within noisy environments over long distance, etc.
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material
24	7x32	TC - Tinned Copper

Conductor Count:	4
Total Number of Pairs:	1

Insulation

Material	Nominal Diameter	Diameter +/- Tolerance
PE - Polyethylene	1.73 mm	0.05 mm

Color Chart

Number	Color
Pair 1	White/Blue & Blue/White
Pair 2	White/Orange & Orange/White

Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]	Thickness of Foil
Tape	1	Bi-Laminate (Alum+Poly)	Beldfoil® (Z-Fold®)	100%	9 / 23 µm
Braid	2	Tinned Copper (TC)		90%	

Outer Jacket Material

Material	Color	Nominal Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	Chrome (RAL 7037)	8.80 mm

Construction and Dimensions

Stranding

Lay Direction	Twists
Left Hand	12 twist/ft

Cabling

Description
2 pairs and 2 fillers twisted to cable core

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
78.7 Ohm/km	7.2 Ohm/1000ft

Impedance

Frequency [MHz]	Nominal Characteristic Impedance
1	120 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	1.97 dB/100m

Delay

Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
66 ns/100m	66%

Current

Max. Recommended Current [A]
2.1 Amps per Conductor

Voltage

Voltage Rating [V]
300 V

Temperature Range

Installation Temp Range:	-15°C To +80°C
Storage Temp Range:	-45°C To +80°C
Operating Temp Range:	-20°C To +80°C
Operating Temp Range (Flexible Install):	-15°C To +80°C
Operating Temp Range (Fixed Install):	-45°C To +80°C

Mechanical Characteristics

Oil Resistance:	IEC 60811-404
Max. Pull Tension:	395 N
Min Bend Radius During Installation:	88 mm

Standards

CPR Euroclass:	Cca-s1a,d1,a1
GENELEC Compliance:	EN 50290-2-27

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Euroclass Cca
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	Yes
Suitability - Oil Resistance:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
IEC 60754-1 (EN50267-1)- Halogen Amount:	Zero
IEC 60754-2 (EN50267-2)- Halogen Acid Gas Amount - Max. Conductivity:	2.5 µS/mm
IEC 60754-2 (EN50267-2)- Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 (EN 61034-2) (VDE 0482-1034) - Smoke Density Min. Transmittance:	80%

Part Number

Variants

Item #	Color	Putup Type	Length	EAN
9842LW.00500	Chrome	Reel	500 m	8719605193681

History

Update and Revision:	Revision Number: 0.30 Revision Date: 12-22-2020
----------------------	---

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.