



Product: [9684](#)

RS232/422 Low Cap, #24-12.5pr, PO, O/A Foil, PVC Jkt, CM, 100Ω

Product Description

Computer EIA RS-232/422 Cable, 24 AWG stranded (7x32) tinned copper conductors, polyethylene insulation, twisted pairs, overall Beldfoil® shield (100% coverage), 24 AWG stranded tinned copper drain wire, PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	rs-232 extended distance applications; rs-423 applications; computer communications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; panel wiring
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors	No. of Pairs
24	7x32	TC - Tinned Copper		12
			1	

Conductor Count:	25
------------------	----

Insulation

Material	Nominal Wall Thickness
PE - Polyethylene	0.016 in

Color Chart

Number	Color
1	White/Blue & Blue/White
2	White/Orange & Orange/White
3	White/Green & Green/White
4	White/Brown & Brown/White
5	White/Gray & Gray/White
6	Red/Blue & Blue/Red
7	Red/Orange & Orange/Red
8	Red/Green & Green/Red
9	Red/Brown & Brown/Red
10	Red/Gray & Gray/Red
11	Black/Blue & Blue/Black
12	Black/Orange & Orange/Black
Single	Gray

Color Chart 2

Number
16

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	24	7x32

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.445 in	0.035 in

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Nominal Conductor DCR	Nominal Outer Shield DCR
16 Ohm/1000ft	24 Ohm/1000ft	12 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
15.5 pF/ft	27.5 pF/ft

Impedance

Nominal Characteristic Impedance
100 Ohm

Delay

Max. Delay Skew
66 ns/100m

Current

Max. Recommended Current [A]
2.1 Amps per Conductor at 25°C

Voltage

UL Description	UL Voltage Rating
UL AWM Style 2919	30 V RMS (UL AWM Style 2919)
CM	300 V RMS (CM)

Temperature Range

Operating Temp Range:	-20°C To +80°C
-----------------------	----------------

Mechanical Characteristics

Bulk Cable Weight:	85 lbs/1000ft
Max. Pull Tension:	133 lbs
Min Bend Radius/Minor Axis:	4.5 in

Standards

NEC/(UL) Compliance:	CM
CEC/C(UL) Compliance:	CM
UL AWM Style Compliance:	2919 (30 V 80°C)

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
MII Order #39 (China RoHS):	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 UL Loading
UL voltage rating:	30 V RMS (UL AWM Style 2919)

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
9684 060500	Chrome	Reel	500 ft	612825257035
9684 0601000	Chrome	Reel	1,000 ft	612825257028

Footnote: C - CRATE REEL PUT-UP.

History

Update and Revision: Revision Number: 0.270 Revision Date: 09-30-2020

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.