



**Product:** [9992](#)

Audio, Control & Instrument, #24-9pr, PO, Individ. Foil, PVC Jkt, CM

### Product Description

Audio, Control & Instrument Cable, 24 AWG stranded (7x32) tinned copper conductors, polyethylene insulation, twisted pairs, individually shielded with Beldfoil® (100% coverage), 24 AWG stranded tinned copper drain wire, PVC jacket.

### Technical Specifications

#### Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	No. of Pairs
24	7x32	TC - Tinned Copper	9

Conductor Count:	18
------------------	----

##### Insulation

Material	Nominal Wall Thickness
PE - Polyethylene	0.011 in

##### Color Chart

Number	Color
1	Black & Red
2	Black & White
3	Black & Green
4	Black & Blue
5	Black & Yellow
6	Black & Brown
7	Black & Orange
8	Red & White
9	Red & Green

##### Inner Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil® (Z-Fold®)	100%	TC - Tinned Copper	24	Stranded

##### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.383 in	0.035 in

#### Electrical Characteristics

##### Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR
18 Ohm/1000ft	24 Ohm/1000ft

##### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
25 pF/ft	47 pF/ft

#### Impedance

Nominal Characteristic Impedance
60 Ohm

#### Delay

Max. Delay Skew
66 ns/100m

#### Current

Max. Recommended Current [A]
1.1 Amps per Conductor at 25°C

#### Voltage

UL Description	UL Voltage Rating
UL AWM Style 2919	30 V RMS (UL AWM Style 2919)
CM	300 V RMS (CM)

#### Temperature Range

UL Temp Rating:	80°C (UL AWM Style 2919)
Operating Temp Range:	-20°C To +80°C

#### Mechanical Characteristics

Bulk Cable Weight:	78 lbs/1000ft
Min Bend Radius/Minor Axis:	4 in

#### Standards

NEC/(UL) Compliance:	CM
CEC/C(UL) Compliance:	CM
UL AWM Style Compliance:	2919 (30 V 80°C)
CPR Euroclass:	Eca

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
MII Order #39 (China RoHS):	Yes

#### Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 UL Loading
IEC Flammability:	IEC 60332-1-2
UL voltage rating:	30 V RMS (UL AWM Style 2919)

#### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

#### Part Number

#### Variants

Item #	Color	UPC
9992 060100	Chrome	612825267737
9992 0601000	Chrome	612825267744
9992 060500	Chrome	612825267751

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

## History

Update and Revision:	Revision Number: 0.258 Revision Date: 02-16-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.