



Product: [9770ZH](#)

Electronic, 3 C #22 Str TC, PO Ins, OS, LSZH Jkt, CMG

[Request Sample](#)

Product Description

Electronic, 3 Conductor 22AWG (7x30) Tinned Copper, PO Insulation, Overall Beldfoil® Shield, LSZH Outer Jacket, CMG

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
22	7x30	TC - Tinned Copper	3

Conductor Count: 3

Insulation

Material	Nominal Wall Thickness
PP - Polypropylene	0.0085 in

Color Chart

Number	Color
1	Black
2	Red
3	White

Outer Shield

Type	Layer	Material	Material Trade Name	Drainwire Material	Drainwire AWG
Tape	Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	TC - Tinned Copper	22

Outer Jacket

Material	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.020 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
15.0 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
32.0 pF/ft	60.0 pF/ft

Current

Max. Recommended Current [A]
3 Amps per Conductor at 25°C

Voltage

UL Voltage Rating

300 V RMS

Temperature Range

UL Temp Rating:	75°C
Operating Temperature Range:	-20°C to 75°C

Mechanical Characteristics

Bulk Cable Weight:	18 lbs/1000ft
Max. Pull Tension:	29 lbs
Min. Bend Radius/Minor Axis:	1.5 in

Standards

NEC Articles:	Article 800
NEC/(UL) Compliance:	CMG
CEC/C(UL) Compliance:	CMG
UL AWM Style Compliance:	AWM 21307

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	UPC
9770ZH 0101000	Black	612825382454
9770ZH 010500	Black	612825382638

History

Update and Revision:	Revision Number: 0.260 Revision Date: 11-09-2022
----------------------	--

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.