



Product: [9BF1-101001](#)

Basic, 15 Amp 10 Outlet NEMA 5-15R PDU with 5-15P



### Product Description

Basic, Standard, 15A, 120V, Horizontal, (10) NEMA 5-15R, 10 ft power cord with 5-15P, Black Powder Coat

### Technical Drawing

#### Belden PDU Specification



Part #: **9BF1-101001**

#### Description:

Basic, Standard, 15A, 120V, Horizontal, (10) NEMA 5-15R, 10 ft power cord with 5-15P, Black Powder Coat



#### Specification:

1.	Quantity Of Inputs	1
2.	Voltage	120V
3.	Current	15A
4.	VA per Input (Load Capacity)	1.4kW
5.	Frequency	50-60 Hz
6.	Over Current Protection	None
7.	Switch	No
8.	Power Cable Wire Gauge	14-2
9.	Power Cable Length	10ft
10.	Plug Type	NEMA 5-15P
11.	Receptacle/Socket Type # 1	NEMA 5-15R
12.	Quantity on Rear	10
13.	Style	Duplex
14.	Maximum Output per Receptacle/Socket	15A
15.	Voltage per Receptacle/Socket	120V
16.	Continuous Operating Temperature Range	0-40C / 50-110F
17.	Heavy Steel - Powder Coat Finish	Black
18.	Configuration	19in / 483mm Horizontal Rackmount
19.	Flush Mount	Yes
20.	Made in the USA	Yes
21.	Product Warranty	5 year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
22.	Certification/Agency Approvals	FURPS Compliant
23.	Certification/Agency Approvals	UL, E & US Listed 60950
24.	Chassis Dimensions (HxWxD)	1.72in x 17in x 3.75in
25.	Shipped Weight	6lbs (2.72kg)
26.	Quantity Of Inputs	1
27.	Voltage	120V

### Technical Specifications

#### Application

Product Overview:	Belden in-cabinet mounted power distribution units (PDUs) and environmental monitors and sensors are designed from high-quality components to support all your mission-critical applications. A key component of our data center ready solution (DCRS), Belden PDUs allow configuration of integrated and optimized hosting systems, including fiber/copper connectivity and cabling, cabinets, cable management and airflow management. They are designed to facilitate seamless integration into Belden racks and cabinets, and include multiple mounting options for maximized airflow and cable management in high-density servers or switch hosting applications. Paired with our extensive line of environmental monitors and sensors, which include alarm thresholds, reporting functionality and built-in intuitive web interface for remote access. Belden has everything you need to precisely monitor, analyze and log key parameters, enabling you to identify current fluctuations and quickly troubleshoot potential problems.
Environmental Space:	Indoor
Power Distribution Type:	Basic (B)

#### Construction and Dimensions

Height:	1.72 in
Width:	17.0 in
Depth:	3.75 in

## Electrical Characteristics

Input Volts (V)/Output Volts (V):	120/120
Amps/Volts:	15/120
Amps/Phases:	15
De-Rated Power (kW):	1.4 kW

## Mechanical Construction

On-Off Switch:	No
Plug Type:	5-15P
Total Receptacle:	10
Receptacle Type/Qty:	5-15R/10
Thermal Circuit Breaker:	No
Cord Length:	10 ft

## Mechanical Characteristics

Mounting:	Horizontal
-----------	------------

## Environmental and Overall Characteristics

Finish:	Black powdercoat finish
Material:	Steel
Color:	Black
Weight:	6.0 lb

## Related Part Numbers

Part Number:	9BF1-101001
Packaging:	Individually Boxed

## Variants

Item #	Color
9BF1-101001	Black

Update and Revision:	Revision Number: 0.33 Revision Date: 04-11-2022
----------------------	-------------------------------------------------

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.