



**Product:** [9841LS](#)

RS 485, 1PR #24 Str TC, PO ins, F/B, LSNH Jkt, 300V SWA

### Product Description

RS 485, 1 Pair AWG 24 Tinned Copper - Stranded, Polyolefin (PO, PE, PP) insulation, Foil + Braid(s) shielding, LSZH / FRNC jacket , 300V SWA

### Technical Specifications

#### Product Overview

Suitable Applications:	RS-485, POS; Computer communications; Low Voltage Analog Signals (4-20ma, 0-10v, ...); Low Voltage Digital Control (24v, ...); Line Level Audio; Panel Wiring; serial communication (RS-485 standard) comprising of PLCs, VFDs, HMI, motors, RTU, SCADA, etc. within noisy environments over long distance, outdoor etc
------------------------	---

#### Construction Details

##### Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	24 AWG	7x32	TC - Tinned Copper

##### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PE - Polyethylene	0.56 mm (0.022 in)	1.73 mm (0.0681 in)	White/Blue & Blue/White

##### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC
Braid	Tinned Copper (TC)	90%	

##### Inner Jacket

Material	Nom. Thickness	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.9 mm (0.035 in)	6.1 mm (0.24 in)

##### Armor

Armor Type & Material	Armor Thickness	Coverage
SWA - Steel Wire Armor	0.9 mm (0.035 in)	Min. 95%

##### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	1.3 mm (0.051 in)	10.3 mm (0.406 in)

Overall Cable Diameter (Nominal):	10.3 mm (0.406 in)
-----------------------------------	--------------------

#### Electrical Characteristics

##### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Pair(s)	78.7 Ohm/km (24.0 Ohm/1000ft)	42 pF/m (13 pF/ft)	75.5 pF/m	120 Ohm	66%	2.1 Amps per Conductor

Nom. Outer Shield DCR: 11 Ohm/km (3.4 Ohm/1000ft)

##### High Frequency (Nominal/Typical)

Element	Frequency [MHz]	Nom. Insertion Loss (Attenuation)
Pair(s)	1	1.97 dB/100m (0.600 dB/100ft)

## Voltage

Voltage Rating
300 V

## Mechanical Characteristics

### Temperature

Operating	Installation	Storage
-45°C To +80°C	-15°C To +80°C	-45°C To +80°C

### Bend Radius

Stationary Min.	Installation Min.
100 mm (3.9 in)	154.5 mm (6.083 in)

Max. Pull Tension: 500 N (110 lbf)

Bulk Cable Weight: 215 kg/km (144 lbs/1000ft)

## Standards and Compliance

Environmental Suitability:	Indoor/Indoor/OutdoorOutdoor/Indoor/Outdoor - Euroclass Eca, Indoor, Outdoor, Non-Halogenated, Sunlight Resistance, Oil Resistance
Flammability / Reaction to Fire:	IEC 60332-3-22, IEC 60332-3-24
CPR Compliance:	CPR Euroclass: Eca
ISO/IEC Compliance:	IEC 61034-2 - Smoke Density Min Transmittance = 60%
GENELEC Compliance:	EN 50290-2-20
European Halogen Free Standards:	IEC 62821-1 Halogen Free Compliance = Yes, IEC 60754-1 - Halogen Amount = Zero, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 2.5 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU CE Mark
UK Regulation Compliance:	UKCA Mark
Other Standard Compliance(s):	DMX-512

## History

Update and Revision: Revision Number: 0.243 Revision Date: 04-07-2025

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	EAN
9841LS.01305	Black	Reel	305 m	8719605022882
9841LS.01500	Black	Reel	500 m	8719605022899
9841LS.011000	Black	Reel	1,000 m	8719605022851
9841LS.011300	Black	Reel	1,300 m	8719605022868
9841LS.011500	Black	Reel	1,500 m	8719605022875
9841LS.021525	Gray	Reel	1,525 m	8719605022905

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.