



Product: [9844LS](#)

RS-485, 4PR #24 Str TC, PO ins, F/B, LSNH Jkt, 300V, SWA

Product Description

RS-485, 4 Pair AWG 24 Tinned Copper - Stranded, Polyolefin (PO, PE, PP) insulation, Foil + Braid(s) shielding, LSZH / FRNC jacket , 300V, SWA

Technical Specifications

Product Overview

Suitable Applications:	RS-485 Instrumentation and computer cable; For EIA RS-485 data transmission applications
------------------------	------------------------------------------------------------------------------------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
24	7x32	TC - Tinned Copper	4

Conductor Count:	8
Total Number of Pairs:	4

Insulation

Material	Nominal Diameter	Diameter +/- Tolerance
PE - Polyethylene	1.73 mm	0.05 mm

Color Chart

Number	Color
Pair 1	White/Blue & Blue/White
Pair 2	White/Orange & Orange/White
Pair 3	White/Green & Green/White
Pair 4	White/Brown & Brown/White

Inner Shield Material

Type	Material	Material Trade Name	Drainwire Material	Drainwire AWG
Tape	Bi-Laminate (Alum+Poly)	Beldfoil® (Z-Fold®)	TC - Tinned Copper	AWG24/7
Braid	Tinned Copper (TC)			

Inner Jacket Material

Material	Color	Nominal Diameter	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	Chrome (RAL 7037)	9.9 mm	0.89 mm

Table Notes:	UV Stabilised
--------------	---------------

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material
Tape		Beldfoil® (Z-Fold®)	100%	TC - Tinned Copper
Braid	Tinned Copper (TC)		90%	

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	15.1 mm	1.35 mm

Construction and Dimensions

Cabling

Description
4 pairs twisted to cable core

Armor

Type of Armor	Material	Thickness of Armoring Wires	Coverage Percentage
Steel Wire Armoring	Galvanized steel wire	1.25 mm	Min. 95%

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
78.7 Ohm/km	6.9 Ohm/km

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
42 pF/m	75.5 pF/m

Impedance

Frequency [MHz]	Nominal Characteristic Impedance
1 MHz	120 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	1.97 dB/100m

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
520 ns/ft	66%

Current

Element	Max. Recommended Current [A]
Conductor	2.1 Amps per Conductor

Voltage

Voltage Rating [V]
300 V

Temperature Range

Installation Temp Range:	-15°C To +80°C
Storage Temp Range:	-45°C To +80°C
Operating Temp Range (Flexible Install):	-15°C To +80°C
Operating Temp Range (Fixed Install):	-45°C To +80°C

Mechanical Characteristics

Oil Resistance:	IEC 60811-404
Max. Pull Tension:	500 N
Min Bend Radius During Installation:	151 mm

Standards

CENELEC Compliance:	EN 50290-2-27
---------------------	---------------

Applicable Environmental and Other Programs

Environmental Space:	Indoor/Outdoor
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-01-01

Suitability

Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	Yes

Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-3-24
IEC 60754-1 (EN50267-1)- Halogen Amount:	Zero
IEC 60754-2 (EN50267-2)- Halogen Acid Gas Amount - Max. Conductivity:	2.5 µS/mm
IEC 60754-2 (EN50267-2)- Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 (EN 61034-2) (VDE 0482-1034) - Smoke Density Min. Transmittance:	IEC 61034-2

Part Number

Variants

Item #	Color	Putup Type	Length	EAN
9844LS.00500	Black	Reel	500 m	8719605023414
9844LS.01500	Black	Reel	500 m	8719605023438
9844LS.001000	Black	Reel	1,000 m	8719605023407
9844LS.011000	Black	Reel	1,000 m	8719605023421

History

Update and Revision:	Revision Number: 0.183 Revision Date: 09-03-2020
----------------------	--------------------------------------------------

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.