



**Product:** [9859](#)

78Ω Twinax, #20 TC, PO, TC Braid

## Product Description

78 Ohm Twinax, 20 AWG stranded (7x28) tinned copper conductor, polyethylene insulation, tinned copper braid shield (85% coverage), non-contaminating PVC jacket.

## Technical Specifications

### Product Overview

Suitable Applications:	Harsh Environment, IIoT, Factory or Process Automation, Video, Audio, Data Communication, etc.
------------------------	--

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Conductors
20	7x28	TC - Tinned Copper	0.038 in	2

Conductor Count:	2
------------------	---

#### Insulation

Material	Nominal Diameter
PE - Polyethylene	.079 in

#### Color Chart

Color
Natural
Natural

#### Outer Shield Material

Type	Material	Coverage [%]
Braid	Tinned Copper (TC)	85%

#### Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride (Non-Contaminating)	0.235 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Outer Shield DCR
9.5 Ohm/1000ft	9.5 Ohm/1000ft		5.3 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
19.7 pF/ft	45.1 pF/ft

#### Inductance

Nominal Inductance
0.119 μH/ft

## Impedance

### Nominal Characteristic Impedance

78 Ohm

## High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.7 dB/100ft
10 MHz	2.3 dB/100ft
50 MHz	5.2 dB/100ft
100 MHz	7.5 dB/100ft
200 MHz	11 dB/100ft
400 MHz	16 dB/100ft

## Delay

Max. Delay Skew	Nominal Delay	Nominal Velocity of Propagation (VP) [%]
66 ns/100m	1.54 ns/ft	66%

## Voltage

### Non-UL Voltage Rating

750 V

Electrical Characteristics Notes: Capacitance Conductor to Other Conductor with Shield: 45.1 pF/ft

## Temperature Range

Operating Temp Range: -40°C to +60°C

## Mechanical Characteristics

Bulk Cable Weight:	30 lbs/1000ft
Max. Pull Tension:	48 lbs
Min Bend Radius/Minor Axis:	2.4 in

## Standards

CPR Euroclass:	Fca
RG Type:	108
Military Compliance:	MIL-DTL-17, M17/45-RG108
Qualified Products List (QPL):	Yes

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	Yes
EU CE Mark:	No
EU RoHS Compliance Date (yyyy-mm-dd):	2005-10-01
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Aerial:	Yes - Black only, when supported by messenger wire
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black only

## Plenum/Non-Plenum

Plenum (Y/N): No

## Part Number

## Variants

Item #	Color	Putup Type	Length	UPC
9859 0101000	Black	Reel	1,000 ft	612825259695

## Product Notes

Notes:	One conductor has a bare copper strand for identification.
--------	--

## History

Update and Revision:	Revision Number: 0.283 Revision Date: 03-16-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.