



REPRESENTATIVE IMAGE

Product: [9886](#)

Audio, Control & Instrument, #20-6pr, PO, Individ. Foil, HDPE Jkt, Direct Burial

Product Description

Audio, Control & Instrument Cable, 20 AWG stranded (10x30) tinned copper conductors, polypropylene insulation, 6 twisted pairs, individually shielded with Beldfoil® (100% coverage), 22 AWG stranded tinned copper drain wire, high-density polyethylene jacket.

Technical Specifications

Product Overview

Suitable Applications:	Low Voltage Analog Signals (4-20ma, 0-10v, ...); Low Voltage Digital Control (24v, ...); Line Level Audio; Computer Communication; Panel Wiring
------------------------	---

Construction Details

Conductor

Element	Number of Element	AWG	Stranding	Material
Pair(s)	6	20	10x30	TC - Tinned Copper

Insulation

Element	Material	Thickness	Color Code
Pair(s)	PP - Polypropylene	0.013 in	Black & Red, Black & White, Black & Green, Black & Blue, Black & Yellow, Black & Brown

Inner Shield Material

Element	Shield Type	Material	Coverage	Drainwire Type	Notes
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (19x34) TC	each pair

Outer Jacket Material

Material	Thickness	Nom. Diameter
PE - Polyethylene	0.045 in	0.455 in

Table Notes:	HDPE
Cable Diameter (Nominal):	0.455 in

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Pair(s)	10.8 Ohm/1000ft	30 pF/ft	55 pF/ft	50 Ohm	66%	2.7 Amps per Conductor at 25°C

Voltage

Non-UL Voltage Rating
350 V

Mechanical Characteristics

Temperature

Operating
-40°C to +80°C

Bend Radius

Stationary Min.	Installation Min.
4.75 in	4.6 in

Max. Pull Tension:	213 lbs
Bulk Cable Weight:	97 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Burial
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.307 Revision Date: 02-16-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.