



Product: [9BO4-301001](#)

Basic, Upgradeable 35 Amp 208V DELTA, 3 Phase, Vertical, (24) Locking IEC C13, (6) Locking IEC C19, PDU with 3P+E CA

Product Description

Basic, Upgradeable, 35A, 208V DELTA, 3 Phase, Vertical, (24) Locking IEC C13, (6) Locking IEC C19, breakerred, 10 ft power cord with 3P+E CA, Black Powder Coat, no Monitoring (Upgradeable with IMD Module)

Technical Drawing

Belden PDU Specification
Part #: 9BO4-301001

Description:
Basic, Upgradeable, 35A, 208V DELTA, 3 Phase, Vertical, (24) Locking IEC C13, (6) Locking IEC C19, breakerred, 10 ft power cord with 3P+E CA, No Monitoring (Upgradeable with IMD module). Black Powder Coat.



Specification:

Table with 35 rows of specifications including Monitoring, Quantity of Inputs, Voltage, Current, VA per Input, Frequency, Over Current Protection, Switch, Power Cable Wire Gauge, Power Cable Length, Power Entry Location, Plug Type, Combined Total Receptacle/Socket Quantity, Receptacle/Socket Type #1, Receptacle/Socket Type #2, Voltage per Receptacle/Socket, Maximum Operating Temperature, Heavy Steel - Powder Coat Finish, Configuration, Vertical Mounting Bracket Kit, Toolless Mounting Hardware - Center to Center Spacing, Made in the USA, Product Warranty, and Certification/Agency Approvals.

Technical Specifications

Application

Table with 3 rows: Product Overview (Belden in-cabinet mounted power distribution units...), Environmental Space (Indoor), and Power Distribution Type (Basic (B)).

Environmental Monitoring:	No
---------------------------	----

## Construction and Dimensions

Height:	72.0 in
Width:	2.0 in
Depth:	2.25 in

## Electrical Characteristics

Amps/Volts:	35/208
Amps/Phases:	35 x 3 Ph
Circuit breaker (Amp/Qty):	20/3D
De-Rated Power (kW):	10.0 kW

## Mechanical Construction

On-Off Switch:	Breaker/Switch Combination
Plug Type:	California Style 50A, 250V, 3P/4W Twistlock
Total Receptacle:	30
Receptacle Type/Qty:	C-13L/24 + C-19L/6
Thermal Circuit Breaker:	Magnetic
Cord Length:	10 ft

## Mechanical Characteristics

Mounting:	Vertical
-----------	----------

## Environmental and Overall Characteristics

Finish:	Black powdercoat finish
Material:	Steel
Color:	Black
Weight:	17.0 lb

## Related Part Numbers

Part Number:	9BO4-301001
Packaging:	Individually Boxed

## Variants

Item #	Color
9BO4-301001	Black

Update and Revision:	Revision Number: 0.28 Revision Date: 04-11-2022
----------------------	---

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.