

**Product:** [9PH2-241007](#) 

Power Metered, 30 Amp 120V 24 Outlet (NEMA 5-20R) PDU with L5-30P Plug

**Product Description**

Metered, Upgradeable, 30A, 120V, Vertical, (24) NEMA 5-20R, breakered, 10 ft power cord with L5-30P, Input current monitoring. Local high visibility LED display. Input power monitoring available via VLC feature using the mobile app. Black Powder Coat

**Technical Drawing**

Belden PDU Specification



Part #: 9PH2-241007

**Description:**

Metered, Upgradeable, 30A, 120V, Vertical, (24) NEMA 5-20R, breakered, 10 ft power cord with L5-30P, Input current monitoring. Local high visibility LED display. Input power monitoring available via VLC feature using the mobile app. Black Powder Coat.



**Specification:**

1. Monitoring	Input current monitoring. Local high visibility LED display. Input power monitoring available via VLC feature using the mobile app.
Monitoring Level 1	Phase (A) Monitoring (kWh, W, VA, PF, V, A)
2.	Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
3. VLC Support	Yes
4. Quantity Of Inputs	1
5. Voltage	120V
6. Current	30A
7. VA per Input (Load Capacity)	2.8kW
8. Frequency	50/60 Hz
9. Over Current Protection	(2) 20A Single Pole Magnetic Breakers
10. Switch	Breaker/Switch Combination
11. Scrolling / Rotatable Digital Display	Yes
12. Power Cable Wire Gauge	10/3
13. Power Cable Length	10ft
14. Power Entry Location	Bottom Front
15. Plug Type	NEMA L5-30P Twistlock
16. Receptacle/Socket Type #1	NEMA 5-20R
17. - Quantity on Face	24
18. - Style	Duplex
19. - Voltage per Receptacle/Socket	120V
20. Internal RMS Voltage Sensor	Yes
21. Internal RMS Current Sensor	Yes
22. Continuous Operating Temperature Range	Full nameplate operation: 10-45C / 50-113F

**Technical Specifications**

**Application**

Product Overview:	Belden in-cabinet mounted power distribution units (PDUs) and environmental monitors and sensors are designed from high-quality components to support all your mission-critical applications. A key component of our data center ready solution (DCRS), Belden PDUs allow configuration of integrated and optimized hosting systems, including fiber/copper connectivity and cabling, cabinets, cable management and airflow management. They are designed to facilitate seamless integration into Belden racks and cabinets, and include multiple mounting options for maximized airflow and cable management in high-density servers or switch hosting applications. Paired with our extensive line of environmental monitors and sensors, which include alarm thresholds, reporting functionality and built-in intuitive web interface for remote access. Belden has everything you need to precisely monitor, analyze and log key parameters, enabling you to identify current fluctuations and quickly troubleshoot potential problems.
Environmental Space:	Indoor
Power Distribution Type:	Power Monitored (P)

Monitoring (Local):	Power
---------------------	-------

## Construction and Dimensions

Height:	66.25 in
Width:	2.0 in
Depth:	2.0 in

## Electrical Characteristics

Amps/Volts:	30/120
Amps/Phases:	30
De-Rated Power (kW):	1.9 kW

## Mechanical Construction

On-Off Switch:	No
Plug Type:	L5-30P
Total Receptacle:	24
Receptacle Type/Qty:	5-20R/24
Surge Suppression:	No
Thermal Circuit Breaker:	No
Cord Length:	10 ft

## Mechanical Characteristics

Mounting:	Vertical
-----------	----------

## Environmental and Overall Characteristics

Finish:	Black Powder Coat
Material:	Steel
Color:	Black
Weight:	15.0 lb

## Related Part Numbers

Part Number:	9PH2-241007
Packaging:	Individually Boxed

## Variants

Item #	Color
9PH2-241007	Black

Update and Revision:	Revision Number: 0.38 Revision Date: 04-11-2022
----------------------	---

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.