

Product: [A5JSJSA6038](#) 



Ethernet/IP CAT5e 1000 Mbps Double-Ended Cordset, male straight transparent RJ45 to male straight transparent RJ45, shielded, PU cable, 8 wires

Product Description

Ethernet/IP CAT5e 1000 Mbps Double-Ended Cordset, male straight transparent RJ45 to male straight transparent RJ45, shielded, PU cable, 8 wires

Technical Specifications

Product Description

Product Family:	EtherNet / IP Double-ended Cordset
Brand:	Lumberg Automation
Connector Type:	RJ45 Male
Shielding Type:	Shielded
Voltage Rating:	60V
Rated Voltage (UL):	30V
Operating Voltage:	30 V
Data Transmission Type:	1000 Mbps

Technical Data Side 1

Side 1 Product Sub Family:	RJ45
Connector Design:	Straight
Number of Pins:	8
Coding, Side 1:	RJ45
Ambient Temperature (Operation)*:	- 25°C to + 70°C
Protection Degree / IP Rating**:	IP20
Housing Material:	PC - Polycarbonate, UL94-V0 rated
Attachment Plating:	Gold plating in contact area
Shielding Material:	Copper Alloy

Cable Data

Cable Type:	26AWG CAT5e S/FTP PVC/PU Patch CABLE
Number of Wires:	8 wires
Cable- resistances:	14.5 Ohm/100m
ISO/IEC Compliance:	ISO/IEC 11801
UL AWM Style Compliance:	AWM 22313
Conductor Material:	Stranded Bare Copper
Cable Jacket Material:	Special Compound Polyurethane
Cable Diameter D:	6.2 mm
Wire Insulation Material:	Polyolefin
Insulated Wire Diameter:	1.08 mm
Foil shield:	Shielding: Each pair with individual foil + overall braid shield
Ambient Temperature (Fixed Installation):	- 20°C to +80°C
Flammability Class (Cable Jacket):	FT2, IEC 603321, IEC 60332-3A
Core Colors:	1: Blue& White, 2: Orange& White, 3: Green& White, 4: Brown& White

Technical Data Side 2

Side 2 Product Sub Family:	RJ45
Connector Design, Side 2:	Straight
Number of Pins, Side 2:	8
Coding, Side 2:	RJ45
Ambient Temperature (Operation), Side 2*:	- 25°C to + 70°C
Protection Degree / IP Rating, Side 2**:	IP20
Housing Material, Side 2:	PC - Polycarbonate, UL94-V0 rated
Attachment Plating, Side 2:	Gold plating in contact area
Shielding Material, Side 2:	Copper Alloy

Safety & Environmental Compliance

RoHS Compliant:	Yes
-----------------	-----

Resistances

Oil Resistance:	Yes
-----------------	-----

Notes

Protection Degree / IP Rating Note:	only if mounted and locked in combination with Hirschmann / Lumberg Automation connector
-------------------------------------	--

History

Update and Revision:	Revision Number: 0.23 Revision Date: 10-26-2025
----------------------	---

Variants

Item #	Cable Length	Color
A5.JS.JSA6038060030	0.3 m	Blue
A5.JS.JSA6038060050	0.5 m	Blue
A5.JS.JSA6038060100	1 m	Blue
A5.JS.JSA6038010100	1 m	Brown
A5.JS.JSA6038020100	1 m	Red
A5.JS.JSA6038030100	1 m	Orange
A5.JS.JSA6038040100	1 m	Yellow
A5.JS.JSA6038050100	1 m	Green
A5.JS.JSA6038070100	1 m	Purple
A5.JS.JSA6038080100	1 m	Gray
A5.JS.JSA6038090100	1 m	White
A5.JS.JSA6038000100	1 m	Black
A5.JS.JSA6038060150	1.5 m	Blue
A5.JS.JSA6038060200	2 m	Blue
A5.JS.JSA6038010200	2 m	Brown
A5.JS.JSA6038020200	2 m	Red
A5.JS.JSA6038030200	2 m	Orange
A5.JS.JSA6038040200	2 m	Yellow
A5.JS.JSA6038050200	2 m	Green
A5.JS.JSA6038070200	2 m	Purple
A5.JS.JSA6038080200	2 m	Gray
A5.JS.JSA6038090200	2 m	White
A5.JS.JSA6038000200	2 m	Black
A5.JS.JSA6038060300	3 m	Blue
A5.JS.JSA6038010300	3 m	Brown
A5.JS.JSA6038020300	3 m	Red
A5.JS.JSA6038030300	3 m	Orange
A5.JS.JSA6038040300	3 m	Yellow
A5.JS.JSA6038050300	3 m	Green
A5.JS.JSA6038070300	3 m	Purple
A5.JS.JSA6038080300	3 m	Gray
A5.JS.JSA6038090300	3 m	White
A5.JS.JSA6038000300	3 m	Black
A5.JS.JSA6038060500	5 m	Blue
A5.JS.JSA6038061000	10 m	Blue

A5JSJSA6038061500	15 m	Blue
A5JSJSA6038062000	20 m	Blue
A5JSJSA6038062500	25 m	Blue
A5JSJSA6038063000	30 m	Blue

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.