



Product: [A03044B](#)

TC VN/PVC, 3+G C #4 Str BC, PVC-NYL Ins M4, Blk PVC Jkt, 600V TC-ER
90C Dry/Wet SUN RES DIR BUR

Product Description

UL Type TC (1277) PVC-Nylon/PVC, 3+G Conductor 4AWG (7x12) Bare Copper, PVC-NYL Insulation M4 Color Code, Black PVC Outer Jacket, 600V TC-ER 90C Dry/Wet SUN RES DIR BUR

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
4	7x12	BC - Bare Copper	3
8		BC - Bare Copper	1

Conductor Count: 3

Insulation

Material	Nominal Diameter
PVC/Nylon - Polyvinyl Chloride + Nylon	0.323 in
No Insulation	

Color Chart

Number	Color
1	Black
2	Black
3	Black

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.822 in	0.063 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
0.26 Ohm/1000ft

Current

Max. Recommended Current [A]
95 Amps per Conductor at 30°C

Voltage

UL Description	UL Voltage Rating	Voltage Rating [V]
TC-ER	600 V RMS (Type TC)	600 V RMS (Type TC)

Temperature Range

UL Temp Rating:	90°C Dry, 90°C Wet
Operating Temp Range:	-25°C To +90°C

Wet Temp Range:	-30°C To +90 °C
Dry Temp Range:	-30°C To +90 °C

Mechanical Characteristics

Min Bend Radius (Overall):	6.576 in
Min Bend Radius/Minor Axis:	3.29 in

Standards

NEC/(UL) Compliance:	TC-ER
----------------------	-------

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01

Suitability

Suitability - Burial:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 Vertical Tray Flame Test
UL voltage rating:	600 V RMS (Type TC)

Part Number

Variants

Item #	Putup Type
A03044B 0105000	Reel

History

Update and Revision:	Revision Number: 0.36 Revision Date: 06-24-2020
----------------------	---

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.