



Product: [ACX-FF-SPLICING](#)



Fiber Splice Kit for FX ACX HD Patch Panel Housing

Product Description

Fiber Splice Kit for FX ACX HD Patch Panel Housing

Technical Specifications

Product Overview

| | |
|------------------------|---|
| Environmental Space: | Indoor |
| Suitable Applications: | FiberExpress ACX Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers |

Construction

| | |
|---------|--------|
| Height: | 34 mm |
| Width: | 92 mm |
| Length: | 155 mm |

Physical Specifications

| | |
|---------------|----------------------------------|
| Max Capacity: | 96 fiber (24f splices per layer) |
|---------------|----------------------------------|

Temperature Range

| | |
|------------------------------|----------------|
| Operating Temperature Range: | -10°C to +60°C |
| Storage Temperature Range: | -10°C to +60°C |

Product Material

Materials

| Description | Material | Color |
|---------------|----------|-------|
| Splice Tray | PC/ABS | Gray |
| Splice Holder | TPE | Gray |

Standards

| | |
|-----------------------------------|-----|
| EU Directive 2011/65/EU (RoHS 2): | Yes |
|-----------------------------------|-----|

Related Part Numbers

| | |
|----------------|---|
| Related Parts: | 1U, 19" Rack mount patch panel housing: ACX-01RM-048P, 4U, 19" Rack mount patch panel housing ACX-04RM-192P |
|----------------|---|

Product Notes

| | |
|--------|---|
| Notes: | Splice Tray Construction: 4 layers (stacked) & Support Splice Type: Heat Shrink Fusion Splice, Accessories Fiber Storage: Spool x 2, Splice Protection Sleeve (50mm length) x 100, Cable Tie (80mm length) x 10, Spiral Tubing (4M) |
|--------|---|

History

| | |
|----------------------|---|
| Update and Revision: | Revision Number: 0.12 Revision Date: 09-30-2024 |
|----------------------|---|

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.