



**Product:** [A1910K](#)

TC VN/PVC, 19 C #10 Str BC, PVC-NYL Ins E2, OS, Blk PVC Jkt, 600V  
TC-ER 90C Dry/Wet SUN RES DIR BUR

### Product Description

UL Type TC (1277) PVC-Nylon/PVC, 19 Conductor 10AWG (7x18) Bare Copper, PVC-NYL Insulation E2 Color Code, Overall Beldfoil® Shield, Black PVC Outer Jacket, 600V TC-ER 90C Dry/Wet SUN RES DIR BUR

### Technical Specifications

#### Product Overview

Suitable Applications:	harsh environment digital and serial two-way communication, oil and gas extraction and refining sites, petrochemical, Profibus process automation or Foundation FieldBus process automation, extreme temperature environments, exposure to humidity/moisture, dust, and oil, remote locations long distance applications, etc.
------------------------	--

#### Physical Characteristics (Overall)

##### Conductor

Element	AWG	Stranding	Material	No. of Conductors
Conductor(s)	10	7x18	BC - Bare Copper	19

Conductor Count:	19
------------------	----

##### Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PVC/Nylon - Polyvinyl Chloride + Nylon	0.164 in	0.026 in

##### Color Chart

Number	Color
1	Black and Numbered 1
2	Red and Numbered 2
3	Blue and Numbered 3
4	Orange and Numbered 4
5	Yellow and Numbered 5
6	Brown and Numbered 6
7	Red/Black and Numbered 7
8	Blue/Black and Numbered 8
9	Orange/Black and Numbered 9
10	Yellow/Black and Numbered 10
11	Brown/Black and Numbered 11
12	Black/Red and Numbered 12
13	Blue/Red and Numbered 13
14	Orange/Yellow and Numbered 14
15	Yellow/Red and Numbered 15
16	Brown/Red and Numbered 16
17	Black/Blue and Numbered 17
18	Red/Blue and Numbered 18
19	Orange/Blue and Numbered 19

##### Outer Shield

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	10

#### Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.990 in	0.083 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR
1.04 Ohm/1000ft

#### Current

Max. Recommended Current [A]
20 Amps per Conductor at 30°C

#### Voltage

Description	UL Description	UL Voltage Rating	Voltage Rating [V]
Type TC	TC	600 V RMS (Type TC)	600 V RMS (Type TC)

### Temperature Range

UL Temp Rating:	90°C Dry, 90°C Wet
Operating Temperature Range:	-30°C To +90°C
Wet Temp Range:	-30°C To +90 °C
Dry Temp Range:	-30°C To +90 °C

### Mechanical Characteristics

UV Resistance:	Yes
Bulk Cable Weight:	927 lbs/1000ft
Max. Pull Tension:	1577 lbs
Min Bend Radius (Overall):	9.9 in
Min. Bend Radius/Minor Axis:	9.90 in

### Standards

NEC/(UL) Compliance:	TC-ER, THWN-2
----------------------	---------------

### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes

### Suitability

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

### Flammability, LSOH, Toxicity Testing

UL Flammability:	UL 1685 UL Loading
IEEE Flammability:	1202
UL voltage rating:	600 V RMS (Type TC)

### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

### History

Update and Revision:	Revision Number: 0.52 Revision Date: 05-31-2024
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.