



Product: [ACX-FFxSyyLD](#)

FX ACX Adapter Frame LC Duplex



Product Description

FX ACX Adapter Frame LC Duplex

Technical Specifications

Product Overview

| | |
|------------------------|---|
| Environmental Space: | Indoor |
| Suitable Applications: | Data Centers, Main Equipment Rooms, Telecommunications Rooms. |

Temperature Range

| | |
|------------------------------|----------------|
| Operating Temperature Range: | -20°C To +60°C |
| Storage Temperature Range: | -20°C To +60°C |

Product Material

Materials

| Description | Material | Color |
|-------------------------|----------------|-------|
| Frame Base Material | SPCC | Black |
| Frame Surface Treatment | Powder Coating | |

Standards

| | |
|-----------------------------------|---------------------------------------|
| TIA/EIA Compliance: | TIA-568.3-E, TIA/EIA-604-10(FOCIS-10) |
| ISO/IEC Compliance: | IEC 11801 |
| EU Directive 2011/65/EU (RoHS 2): | Yes |

Related Part Numbers

| | |
|----------------|---|
| Related Parts: | FX ACX HD Patch Panel Housing (Part Number: ACX-01RM-048P & ACX-04RM-192P). |
|----------------|---|

Variants

| Item # | Port Count |
|--------------|------------|
| ACX-FFSS06LD | 6 Port |
| ACX-FFSS06LA | 6 Port |
| ACX-FF3S06LD | 6 Port |
| ACX-FF4S06LD | 6 Port |
| ACX-FF5S06LD | 6 Port |
| ACX-FFSS12LD | 12 Port |
| ACX-FFSS12LA | 12 Port |
| ACX-FF3S12LD | 12 Port |
| ACX-FF4S12LD | 12 Port |
| ACX-FF5S12LD | 12 Port |

Product Notes

| | |
|------------|--|
| Packaging: | Individually packaged in a sealed plastic bag. |
|------------|--|

Notes: ACX-FFSSyLD is SM (adaptor color is Blue), ACX-FFSSyLA is SM APC (adaptor color is Green), ACX-FF3SsyLD is MM OM3 (adaptor color is Aqua), ACX-FF4SsyLD MM OM4 (adaptor color is Erika Violet), ACX-FF5SsyLD MM OM5 (adaptor color is Lime Green).

History

Update and Revision: Revision Number: 0.4 Revision Date: 08-27-2024

© 2024 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.