



Product: [AP100045](#)



Fiber Wall Mount Patch Panel with Lock, Black

Product Description

Fiber Wall Mount Patch Panel with Lock, Black

Technical Specifications

Product Overview

| | |
|------------------------|--|
| Environmental Space: | Indoor |
| Suitable Applications: | Space saving: the compact dimension (56.8mm*322.6mm*253.6mm) is suitable for applications with limited space, Flexible design for fiber accommodation: Support up to 24 fibers (LC connector), 12 fibers (SC connector), Splice tray and kit: support for fiber splicing and cable management, Lockable door to restrict unauthorized access, Easy installation and maintenance: foldable door is easy for installation and maintenance. |

Construction

| | |
|---------|----------|
| Height: | 253.6 mm |
| Width: | 322.6 mm |
| Depth: | 56.8 mm |

Physical Specifications

| | |
|---------------|-----------------------------|
| Max Capacity: | upto 24F (LC adapter Strip) |
|---------------|-----------------------------|

Product Material

Materials

| Description | Material |
|-------------|----------|
| Panel | Aluminum |

Standards

| | |
|---------------------|------------|
| ISO/IEC Compliance: | ISO 2768-1 |
|---------------------|------------|

Related Part Numbers

| | |
|-----------------|---|
| Included Parts: | Wire management saddles, Velcro tapes, Fiber heat shrink tube, Lock key |
| Related Parts: | This wall mount fiber patch panel is fully compatible with Belden fiber adapter strip & KeyConnect Frame (AP100065). KeyConnect Frame can support 6 ports unshielded KeyConnect modular jack or KeyConnect LC & SC adapter. Please contact our sales representatives for further information. |

Variants

| Item # | Color |
|----------|-------|
| AP100045 | Black |

Product Notes

| | |
|--------|--|
| Notes: | AP100065 KeyConnect Frame, KeyConnect modular jack or KeyConnect LC & SC adapters need to be purchased separately. Rubber Gromment Diameter: ø 28 mm |
|--------|--|

History

| | |
|----------------------|---|
| Update and Revision: | Revision Number: 0.20 Revision Date: 08-13-2023 |
|----------------------|---|

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.