



Product: [AP900002](#)

19", 42U, 800(W)x1100(D) Network Cabinet with Aluminum Frame and Front/Rear Split Doors, Black

Product Description

19", 42U, 800(W)x1100(D) Network Cabinet with Aluminum Frame and Front/Rear Split Doors, Black

Technical Specifications

Application

Product Overview:	Cabinet-19" vertical rail:Aluminum Alloy, Side Panels & Doors Material:Cold rolled powder coated steel, Side Panels:Split side panel provide convenient access for the equipment installation, Rails Depth adjustable:Depth adjustable 19" vertical mounting rails compatible with mainstream IT equipment, Rails Indications:RU numbers printed on the 19" rails, Casters:The cabinet equipped with casters are easy for the cabinet deployment, PDU Rails:PDU rails provide management for the power and cable. Note:Cabinet accessory need to be purchased separately. Accessories-Fixed Shelf:AP900010, Vertical Cable Manager:AP900008, Blank Panel:AP900003, Fan Top Unit:AP900004, E-lock with IC card:AP900005, Top cap brush:AP900013
Features:	For housing electronics hard ware like servers, switches, Copper and Fiber panels etc in a variety of environment like Server rooms, Network rooms, Data Centers etc.
Environmental Space:	Indoor

Construction and Dimensions

Rack Units:	42U
Height:	1955* mm
Width:	800 mm
Depth:	1100 mm

Mechanical Construction

Mechanical Construction Note:	*Overall height of cabinet without casters
Door Type:	Split doors with approx. 70% airflow by mesh pattern

Mechanical Characteristics

Mechanical Characteristics Note:	Relative Humidity:≤ 85%, IP Rating:IP 20
Load Capacity - Static:	1200 kg

Environmental and Overall Characteristics

Operating Temperature Range:	-5°C to +65°C
Storage Temperature Range:	-25°C to +55°C
Color:	Black

Standards

ANSI Compliance:	ANSI/EIA RS-310-E
------------------	-------------------

Related Part Numbers

Part Number:	AP900002
Included Parts:	PDU rails (2x), Side panels (4x), Casters & Heavy duty leveling legs (4x)

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.