



Product: [ACP-A](#)

XTran PSU 110-220 VAC for XT-1104-A, XT-2206-A, XT-2209-A and XT-2210-A nodes

Product Description

XTran AC Power Supply with 110-220 VAC input for XT-1104-A, XT-2206-A, XT-2209-A, XT-2210-A

Technical Specifications

Product Overview

Part Number:	V30912-A5020-A1
Power Supply Protection:	Auto restart: Over temperature / Overcurrent
Power Supply Efficiency:	At 230VAC and Pout is 220W: 91%; At 110VAC and Pout is 220W: 87%
Output Power:	220W

Power requirements

Input voltage:	100 - 240 VAC $\pm$ 10% (50-60Hz)
Inrush Current Max:	Cold start 230VAC: 30A

Ambient conditions

MTBF (MIL-HDBK 217F: Gb 25 °C):	34 Years
Operating Temperature Range:	-30° to +65°C (-22° to 149°F)
Storage Temperature Range:	-30° to +75°C (-22° to 167°F)
Relative humidity (non-condensing):	0-95 %

Mechanical construction

Overall Width:	40.32 mm
Overall Height:	126 mm
Depth:	193 mm
Weight:	0.91 kg
Power Supply Connector:	IEC320 on front panel
Node Compatibility:	XT-1104-A, XT-2206-A, XT-2209-A, XT-2210-A

Approvals

Basis Standard:	CE, EN 55032:2015 + A11:2020, EN IEC 61000-3-2:2019, EN 61000-3-3:2013 + A2 :2021, EN 55035:2017 + A11:2020, EN IEC 61000-6-1:2019, EN IEC 61000-6-2:2019, EN IEC 61000-6-3:2021, EN IEC 61000-6-4:2019
Safety of industrial control equipment:	EN 62368-1:2014
Power Utility:	EN 61000-6-5:2015, EN 61850-3:2014 (§6.7), IEEE 1613-2009 (§4), IEEE1613-2013 (clause 5,7,8,9,10)
Transportation:	EN 50121-4:2016 + A1:2019

Reliability

Guarantee:	Standard 1 year (extension possible)
------------	--------------------------------------

Scope of delivery and accessories

Accessories to Order Separately:	EU AC power cord with IEC lock - 2.5m: V30812-A3060-A9; UK AC power cord with IEC lock - 2.5m: V30812-A3060-A12; US AC power cord with IEC lock - 2.5m: V30812-A3060-A13
----------------------------------	--

Further Instructions

Product Documentation:	Available via Belden Solutions Portal site
Certificates:	Available via Belden Solutions Portal site

History

Update and Revision:	Revision Number: 0.23 Revision Date: 11-14-2025
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.