




Product: [AP100046](#)



Copper and Fiber Multipurpose Patch Panel

Product Description

1U/19" unshielded patch panel with 24 ports that can accommodate Belden KeyConnect unshielded RJ45 module or Belden KeyConnect LC Duplex Fiber Adapter Module, which makes it possible to combine the fiber and copper category cables into one patch panel. Unoccupied ports can be snapped in blank inserts

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	This hybrid patch panel applicable for Fiber Express Solutions for Backbone, Telecommunications Room, Main Distribution Room and Data Centers along with Copper solution compatible with a variety of modulars that are suitable for use with Cat6A, Cat6 and Cat5e systems.

Construction

Weight:	4.0 kg
Height:	43.2 ± 0.3 mm
Width:	19 in
Depth:	370 mm

Physical Specifications

Max Capacity:	24 ports (KeyConnect Module jack), 24 Fibers (SC); 48 Fibers (LCD)
---------------	--

Mechanical Characteristics

Termination Type:	Front Sliding Drawer
-------------------	----------------------

Temperature Range

Operating Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C

Standards

MII Order #39 (China RoHS):	EUP 50
-----------------------------	--------

Related Part Numbers

Included Parts:	ABS injection-molded splice tray pre-loaded in the panel, Velcro Straps, cable ties, PG13.5 water joint, Heat-shrink tubing, Keystone Blank Inserts for unoccupied ports.
Related Parts:	KeyConnect modular jack, SC simplex adapters or LC Duplex adapter part no. is AP100020~AP100024 and shall be purchased separately.

Variants

Item #	Color
AP100046	Black

Product Notes

Packaging:	Individually packaged in a cardboard box
Notes:	Installation guide for the fiber adapter module:PX103826

History

Update and Revision: Revision Number: 0.30 Revision Date: 04-08-2022

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.