



Product: [AP100065](#)



KeyConnect Empty Frame, 6 Ports, Black

Product Description

KeyConnect Empty Frame, 6 Ports, Black

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	Compatible with AP100045 wall mount fiber patch panel

Construction

Weight:	0.23 lbs
Height:	38 mm
Width:	155 mm

Physical Specifications

Max Capacity:	6 ports, Unshielded KeyConnect modular jack or KeyConnect LC & SC adapter
---------------	---

Mechanical Characteristics

Footprint/Type:	KeyConnect
-----------------	------------

Temperature Range

Operating Temperature Range:	-10°C to +60°C
Storage Temperature Range:	-40°C to +70°C

Product Material

Materials

Description	Material	Color
Frame	SPCC (Steel)	Black

Standards

ISO/IEC Compliance:	ISO 2768-1
MII Order #39 (China RoHS):	EUP 50

Related Part Numbers

Related Parts:	AP100045 wall mount fiber patch panel is fully compatible with Belden fiber adapter strip & KeyConnect Frame (AP100065). KeyConnect Frame can support 6 ports unshielded KeyConnect modular jack or Key Connect LC & SC adapter. Please contact our sales representatives for further information.
----------------	--

Variants

Item #	Color	Connector Type	Port Count
AP100065	Black	KeyConnect	6 Port

Product Notes

Packaging:	Individually packaged in a clear plastic bag
Notes:	KeyConnect modular jack or Key Connect LC & SC adapters need to be purchased separately

History

Update and Revision:	Revision Number: 0.24 Revision Date: 04-08-2022
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.