



Product: [AP100690](#)



100-pair with 5-pair Connecting Blocks, 1U, Rack Mount, 110 Cross-Connect System

Product Description

100-pair with 5-pair connecting blocks, 1U, 19" rack mount 110 cross connect assembly

Technical Specifications

Product Overview

Suitable Applications:	110 Cross-Connect System uses high reliability Insulation Displacement Connection (IDC) contacts to provide high performance connections for voice and data distribution systems
------------------------	--

Physical Characteristics (Overall)

Height:	44.40 mm
Width:	482.60 mm
Depth:	37.50 mm
Packaging:	Individually packaged in a cardboard box.

Connectors

Materials

Description	Material	Type
Front Connection	Steel	Flush
Rear Connection	Phosphor Bronze Alloy with Sn Alloy	IDC
Connector Body	High-Impact, Flame-Retardant Plastic with UL 94-V0	Housing

Construction and Dimensions

Max Capacity:	100 Pair
---------------	----------

Electrical Characteristics

Dielectric Strength:	1000Vac for 1min, No Breakdown
Insulation Resistance:	500MOhm at 100Vdc

Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

Mechanical Characteristics

Termination Interface

Durabilities
Not Less than 20cycles

Applicable Environmental and Other Programs

EU Directive 2011/65/EU (RoHS 2):	Yes
-----------------------------------	-----

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Related Part Numbers

Variants

Item #	Color
AP100690	Black

Product Notes

Included Parts:	1U, 19" Base, 5-pair Blocks, Label Holder, Designation Label
Notes:	Transmission Performance : Exceeds the channel and permanent link requirements of ANSI/TIA 568.2-D Category 5e standard. IDC Wire Gauge : 22AWG~26AWG

History

Update and Revision:	Revision Number: 0.16 Revision Date: 04-08-2022
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.