



Product: [ASB 2-RKT 4-3-632](#) 

M12 Micro splitter cordset, double-ended, M12-duo, male straight to two M12, female straight connectors with self-locking threaded joint, yellow PVC 22 gauge molded cable.

Product Description

M12 Micro splitter cordset, double-ended, M12-duo, male straight to two M12, female straight connectors with self-locking threaded joint, yellow PVC 22 gauge molded cable.

Technical Specifications

Product Description

Product Family:	Sensor / Actuator Connectors
Brand:	Lumberg Automation
Connector Type:	T-Splitter
Voltage Rating:	50 V AC / 60 V DC
Rated Impulse Voltage:	1,5 kV

Technical Data Side 1

Side 1 Product Sub Family:	M12 Splitter
Attachment Type:	Self-locking
Number of Pins:	3
Side 1 Contact Resistance:	≤ 5 mOhm
Insulation Resistance:	> 10 ⁹ Ohm
Ambient Temperature (Operation)*:	-40°C to +90°C (notice derating)
Protection Degree / IP Rating**:	IP 67 / NEMA 6P
Contact Base Material:	CuZn
Side 1 Contact Plating:	Ni/Au
Contact Bearer Material:	TPU
Contact Bearer Color:	Yellow
O-Ring Material:	FKM

Cable Data

Cable Number:	632
Number of Wires:	3
Cable Jacket Material:	PVC
Cable Jacket Color:	Yellow
Cable Diameter D:	0.190"

Safety & Environmental Compliance

RoHS Compliant:	Yes
-----------------	-----

Notes

Variants

Item #	Item Description
600000079	ASB 2-RKT 4-3-632/1.5M
600000080	ASB 2-RKT 4-3-632/1M
600000081	ASB 2-RKT 4-3-632/2M

600001638	ASB 2-RKT 4-3-632/0.3M
600002442	ASB 2-RKT 4-3-632/0.6M
600002547	ASB 2-RKT 4-3-632/5M
600002548	ASB 2-RKT 4-3-632/10M
600002918	ASB 2-RKT 4-3-632/3M

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.