



Product: [AX100695-S](#)

110 CROSS-CONNECT, 300PR LEGS 4PR

Product Description

110 CROSS-CONNECT 300-PAIR KIT (C4) WITH LEGS

Technical Specifications

Product Overview

Suitable Applications:	IBDN System 1200, TIA Category 5e, ISO Class D, 1000BASE-T
------------------------	--

Physical Characteristics (Overall)

Port Count:	300-PAIR
Packaging:	Individually packaged in a clear plastic bag
Weight:	2.382 g

Connectors

Materials

Description	Material
Block	Plastic - UL94V-0

Electrical Characteristics

Dielectric Strength:	1,000V RMS @ 60 Hz for 1 minute kV DC
Current Rating:	1.5 A
Insulation Resistance:	100 MOhm*km
Max Contact Resistance:	1 mOhm

Mated Connection

Frequency (MHz)	Max. Insertion Loss TIA* (dB)	Min. NEXT TIA* (dB)	Min. FEXT TIA* (dB)	Min. FEXT Belden** (dB)	Min. Return Loss TIA* (dB)
100	0.4 dB	43 dB	35.1 dB	36 dB	20 dB

Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

Mechanical Characteristics

Footprint/Type:	110
Tool Compatibility:	110 Cross-Connect Connecting Tool AX100749

Termination Interface

Termination	Connection	Durabilities
Front	IDC Connection	200 insertions

Dimensions (WxHxD)

Width	Height	Depth
10.69	10.78	3.33

Standards

TIA/EIA Compliance:	ANSI/TIA/EIA 568 C.2 Category 5e
---------------------	----------------------------------

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive Compliance:	EU Directive 2002/95/EC (RoHS)

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

Safety Listing:	UL 1863 and CSA-C22.2
-----------------	-----------------------

Related Part Numbers

Related Parts:	110 CROSS-CONNECT CABLE MANAGEMENT TROUGH WITH & WITHOUT LEGS, 110 CROSS-CONNECT PATCH CORDS, 110 CROSS-CONNECT LABEL STRIP
----------------	---

Variants

Item #	Color	UPC
AX100695-S	Almond	611589001984

Product Notes

Included Parts:	1x300-PAIR WIRING BLOCK, 75xCONNECTING BLOCK 4-PAIR
Notes:	For additional information about this product, visit our web site at http://www.belden.com

History

Update and Revision:	Revision Number: 0.73 Revision Date: 03-04-2023
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.