

**Product:** [AX102677](#) 

10GX IDC Block Support



## Product Description

10GX IDC Block Support XConnect, 6-port, Black (Empty)

## Technical Specifications

### Product Overview

Suitable Applications:	Compatible with Cross-Connect Application or Consolidation Point Application for use with Belden IBDN Systems 10GX, 4800, 2400 and 1200.
------------------------	--

### Physical Characteristics (Overall)

Port Count:	6 connectors
Packaging:	Packaged 12 units per bag
Weight:	0.07 g

### Connectors

#### Materials

Description	Material
Block Support	Lexan

### Electrical Characteristics

#### Inductance

Nominal Inductance
0.16 $\mu$ H/m
0.16 $\mu$ H/ft

### Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

### Mechanical Characteristics

#### Dimensions (WxHxD)

Width	Height	Depth
6.64	0.97	1.45

### Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU Directive Compliance:	EU Directive 2002/95/EC (RoHS)

### Suitability

Suitability - Indoor:	Yes
-----------------------	-----

### Flammability, LS0H, Toxicity Testing

Safety Listing:	UL 1863 and CSA-C22.2
-----------------	-----------------------

## Related Part Numbers

Related Parts:	10GX IDC Connecting Block
----------------	---------------------------

### Variants

Item #	Color	UPC
AX102677	Black	611589005449

## Product Notes

Notes:	For proper installation refer to Installation Guide PX104200 included with the product or visit our web site at <a href="http://www.belden.com/pdfs/Techpprs/InstallationGuide.pdf">http://www.belden.com/pdfs/Techpprs/InstallationGuide.pdf</a>
--------	---

## History

Update and Revision:	Revision Number: 0.86 Revision Date: 04-08-2022
----------------------	---

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.