



Product: [BASES E-SERIES](#) 

EDAB2xxx - Series



Product Description

Bases for E-Series Cabinets with knockouts for cable entry. The base is constructed out of two side profiles which correspond to the depth of the cabinet, and two cover panels (front and back) with a corresponding width. .

Technical Specifications

Application

Suitable Applications:	Bases can be used to lift the cabinet to provide cable access from underneath. Support maximum capacity of 1900kg.
Environmental Space:	Indoor

Construction and Dimensions

Height:	120 mm
---------	--------

Mechanical Construction

Mechanical Construction Note:	TIP: The base is prepared for installation of stabilisers EDAB101x, which are highly recommended to use on cabinets with sliding servers.
-------------------------------	---

Mechanical Characteristics

Load Capacity:	1900 kg
----------------	---------

Environmental and Overall Characteristics

Finish:	Powder Coated
Material:	Steel

Standards

EU Directive 2011/65/EU (RoHS 2):	Yes
MII Order #39 (China RoHS):	EUP 50

Related Part Numbers

Included Parts:	2x side base profile with a cable entry (with knockout-type blanking panels), 2x cover with cable entry (with knockout-type blanking panels), 1 cover with filter, 1 anti dust brush, fasteners
Packaging:	Individually packed.

Variants

Item #	Width	Depth	Color	Application
EDAB2611	600	1,000	Gray	E-Series Cabinets
EDAB2612	600	1,000	Black	E-Series Cabinets
EDAB2621	600	1,200	Gray	E-Series Cabinets
EDAB2622	600	1,200	Black	E-Series Cabinets
EDAB2681	600	800	Gray	E-Series Cabinets
EDAB2682	600	800	Black	E-Series Cabinets
EDAB2811	800	1,000	Gray	E-Series Cabinets
EDAB2812	800	1,000	Black	E-Series Cabinets
EDAB2821	800	1,200	Gray	E-Series Cabinets
EDAB2822	800	1,200	Black	E-Series Cabinets
EDAB2881	800	800	Gray	E-Series Cabinets

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.