



Product: [BE41339](#)

Lead Wire, #8 Str BC, PVC Ins, AWM 1017

Product Description

UL AWM ST1017 VW1 8AWG/NX41B CSA TEW FT1

Technical Specifications

Product Overview

Suitable Applications:	UL Appliance Wiring Material Subject 758 Style 1017, 80C, 600 volt, VW-1, oil 60C; CSA Equipment wires C22.2 no. 127 Type TEW, 105C, 600V, FT1, oil 60C
------------------------	---

Construction Details

Conductor

Size	Stranding	Material	Notes
8 AWG	Stranded	BC - Bare Copper	Construction: 2156x0.071

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter
PVC - Polyvinyl Chloride	1.19 mm (0.0469 in)	7.5 mm (0.30 in)

Electrical Characteristics

Voltage

UL Voltage Rating
600 V

Mechanical Characteristics

Temperature

UL Temperature
80°C (CSA 105°C)

Standards and Compliance

Environmental Suitability:	Indoor, Oil Resistance
Flammability / Reaction to Fire:	VW-1
AWM Compliance:	AWM 1017, TEW
Military Compliance:	N/A

History

Update and Revision:	Revision Number: 0.170 Revision Date: 03-04-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
BE41339.041400	Blue	Reel	1,400 m	8719605025678
BE41339.031400	Red	Reel	1,400 m	8719605025661
BE41339.01500	Yellowgreen	Reel	500 m	8719605025630

BE41339.011400	Yellowgreen	Reel	1,400 m	8719605025623
----------------	-------------	------	---------	---------------

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.