



Product: [BE41490](#)

Lead Wire, #12 Str TC, PVC Ins, AWM 1015

Product Description

UL AWM ST1015 VW1 12AWG/56X29T CSA TR32

Technical Specifications

Product Overview

Suitable Applications:	UL Appliance Wiring Material Subject 758 Style 1015, 80C, 600 volt.; IEC-65 Internal wiring; CSA-C22.2 no. 16 Type TR-32 90C, 1400 volt peak
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Construction n x D
12	Stranded	TC - Tinned Copper	56x0.30 mm

Conductor Count:	1
------------------	---

Insulation

Type	Material	Nominal Diameter	Diameter +/- Tolerance	Min. Wall Thickness	Nominal Wall Thickness
Insulation	PVC - Polyvinyl Chloride	4.22 mm	0.07 mm	0.71 mm	0.79 mm

Construction and Dimensions

Min Elongation at Breakof Conductors:	5 %
---------------------------------------	-----

Electrical Characteristics

Conductor DCR

Element	Max. Conductor DCR
Conductor(s)	5.1 Ohm/km

Voltage

UL Voltage Rating
600 V

Temperature Range

UL Temp Rating:	80°C
-----------------	------

Standards

UL AWM Style Compliance:	UL AWM 1015
CSA Rating:	CSA-C22.2 no. 16 Type TR-32
Military Compliance:	N/A

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU CE Mark:	On label
EU RoHS Compliance Date (yyyy-mm-dd):	2005-01-01

Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	VW-1
UL voltage rating:	600 V RMS

Part Number

Variants

Item #	Color	Putup Type	Length	EAN
BE41490.00300	Black	Reel	300 m	8719605025814
BE41490.05300	Blue	Reel	300 m	8719605025869
BE41490.04300	Gray	Reel	300 m	8719605025852
BE41490.06300	Purple	Reel	300 m	8719605025876
BE41490.03300	Red	Reel	300 m	8719605025845
BE41490.02300	Yellow	Reel	300 m	8719605025838
BE41490.01300	Yellow, Green Stripe	Reel	300 m	8719605025821

History

Update and Revision:	Revision Number: 0.142 Revision Date: 07-26-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.