



Product: [BE41508](#)

Lead Wire, #8 Str BC, PVC Ins, AWM 1017

Product Description

UL AWM ST1017 VW1 8AWG/168X30B CSA TEW FT1

Technical Specifications

Product Overview

Suitable Applications:	UL Appliance Wiring Material Subject 758 Style 1017, 80C, 600 Vac.; CSA Type TEW, FT1
------------------------	---

Physical Characteristics (Overall)

Conductor			
AWG	Stranding	Material	Construction n x D
8	Stranded	BC - Bare Copper	168x0.254 mm
Conductor Count:		1	

Insulation					
Type	Material	Nominal Diameter	Diameter +/- Tolerance	Min. Wall Thickness	Nominal Wall Thickness
Insulation	PVC - Polyvinyl Chloride	6.7 mm	0.1 mm	1.01 mm	1.14 mm

Electrical Characteristics

Conductor DCR	
Element	Max. Conductor DCR
Conductor(s)	2.06 Ohm/km
Min Insulation Resistance:	0.762 MOhm*km

Voltage	
UL Voltage Rating	600 V

Temperature Range

UL Temp Rating:	80°C
-----------------	------

Standards

UL AWM Style Compliance:	AWM 1017
Military Compliance:	N/A

Applicable Environmental and Other Programs

Environmental Space:	Indoor
EU CE Mark:	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	VW-1
CSA Flammability:	FT1
UL voltage rating:	600 V RMS

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	EAN
BE41508.00300	Black	Reel	300 m	8719605026170
BE41508.001500	Black	Reel	1,500 m	8719605026163
BE41508.05300	Blue	Reel	300 m	8719605026279
BE41508.051500	Blue	Reel	1,500 m	8719605026262
BE41508.031500	Brown	Reel	1,500 m	8719605026224
BE41508.04300	Red	Reel	300 m	8719605026255
BE41508.041500	Red	Reel	1,500 m	8719605026248
BE41508.02300	Violet	Reel	300 m	8719605026217
BE41508.021500	Violet	Reel	1,500 m	8719605026200
BE41508.01300	Yellow, Green Ring	Reel	300 m	8719605026194
BE41508.011500	Yellow, Green Ring	Reel	1,500 m	8719605026187

History

Update and Revision:	Revision Number: 0.165 Revision Date: 04-08-2022
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.