



Product: [BE43780](#)

Lead Wire, #8 Str TC, PVC Ins, AWM 1034

Product Description

UL AWM ST 10434 VW-1 8AWG / 168x30 T

Technical Specifications

Product Overview

Suitable Applications:	Rated temperature UL max 80 C and CSA max 105 C; Rated voltage max 600 V ac, 750 V dc and 2500 Volts peak for electronic use only; Internal Wiring of Appliances; or Internal Wiring of Appliances where exposed to oil at a temperature not exceeding 60 C
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material
8	168x30	TC - Tinned Copper

Conductor Count: 1

Insulation

Layer	Type	Material	Nominal Diameter	Diameter +/- Tolerance	Nominal Wall Thickness	Color
1	Insulation	PVC - Polyvinyl Chloride	6.8 mm	0.05 mm		
2		PVC - Polyvinyl Chloride	8 mm	0.12 mm	0.6 mm	Mushroom (RAL 9002)

Color Chart

Number	Color
Wire 1	Yellow/Green

Construction and Dimensions

Cabling

Description
1 wire

Temperature Range

UL Temp Rating: 80°C

Standards

UL AWM Style Compliance:	AWM 10434
Military Compliance:	N/A

Applicable Environmental and Other Programs

Environmental Space: Indoor

Flammability, LSOH, Toxicity Testing

UL voltage rating: N/A

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	EAN
BE43780.001000	Beige	Reel	1,000 m	8719605026538

History

Update and Revision:	Revision Number: 0.148 Revision Date: 04-08-2022
----------------------	--

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.