



Product: [AX102680](#)

10GX IDC Rear X-BAR

Product Description

10GX IDC Connecting Block Rear X-Bar, Orange

Technical Specifications

Product Overview

Suitable Applications:	- Compatible with Cross-Connect Application or Consolidation Point Application for use with Belden IBDN Systems 10GX, 4800, 2400 and 1200.
------------------------	--

Physical Characteristics (Overall)

Insulation

Nominal Diameter	
0.169 mm	
Packaging:	Packaged 100 units per bag
Weight:	0.01 g

Connectors

Materials

Description	Material
Rear X-Bar	Lexan

Electrical Characteristics

Inductance

Nominal Inductance	
0.169 μ H/m	

Temperature Range

Installation Temperature Range:	-10°C To +60°C
Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

Mechanical Characteristics

Footprint/Type:	IDC
-----------------	-----

Dimensions (WxHxD)

Width	Height	Depth
0.68	0.35	0.308

Standards

Data Category:	Category 6A
----------------	-------------

Applicable Environmental and Other Programs

Environmental Space:	Indoor
----------------------	--------

EU Directive Compliance:	EU Directive 2002/95/EC (RoHS)
--------------------------	--------------------------------

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

Safety Listing:	UL 1863 and CSA-C22.2
-----------------	-----------------------

Related Part Numbers

Related Parts:	10GX IDC Connecting Block
----------------	---------------------------

Variants

Item #	Color	UPC
AX102680	Orange	611589005463

Product Notes

Notes:	For proper installation refer to Installation Guide PX104200 included with the product or visit our web site at http://www.belden.com/pdfs/Techpprs/InstallationGuide.pdf
--------	---

History

Update and Revision:	Revision Number: 0.92 Revision Date: 03-04-2023
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.