



Product: [AdvanceNet Category 6e CMP](#) 

Category 6+ Premium Cable, 4 Pair, U/UTP, CMP

Product Description

Category 6+ Premium Premise Horizontal Cable (400MHz), 4 Pair, 23 AWG Solid Bare Copper Conductors, U/UTP, Plenum-CMP, Flamarrest® PVC-LS Jacket

Technical Specifications

Product Overview

Suitable Applications:	Premise Horizontal Cable, Ethernet 1000BASE-T, Ethernet 100BASE-TX, Ethernet 10BASE-T, PoE++, PoE+, PoE
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/patents .

Construction Details

Conductor

Size	Stranding	Material
23 AWG	Solid	BC - Bare Copper

Insulation

Material	Color Code
PO+FEP - Polyolefin + Fluorinated Ethylene Propylene	White/Blue Stripe & Blue, White/Orange Stripe & Orange, White/Green Stripe & Green, White/Brown Stripe & Brown

Outer Jacket

Separator	Material	Material Trade Name	Nom. Diameter	Ripcord
Center Member (Patented X-Spline®)	PVC - Polyvinyl Chloride	Flamarrest®	0.238 in (6.05 mm)	Yes

Overall Cable Diameter (Nominal):	0.238 in (6.05 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Capacitance Unbalance
77 Ohm/km (23 Ohm/1000ft)	330 pF/100m

Delay

Frequency	Max. Delay	Max. Delay Skew	Nom. Velocity of Prop.	Typical Delay Skew
100 MHz	537.6 ns/100m	35 ns/100m	70%	35 ns/100m

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation) [dB/100m]	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted) [Ohm]
1	2.0	84.3	82.3	80.3	80.3	76.8	73.8	20.0	100 ± 15
4	3.7	75.3	73.3	69.5	69.5	64.8	61.8	23.6	100 ± 15
8	5.3	70.8	68.8	63.5	63.5	58.7	55.7	25.3	100 ± 15
10	5.9	69.3	67.3	61.4	61.4	56.8	53.8	26.0	100 ± 15
16	7.4	66.2	64.2	56.8	56.8	52.7	49.7	26.0	100 ± 15
20	8.3	64.8	62.8	54.4	54.4	50.8	47.8	26.0	100 ± 15
25	9.4	63.3	61.3	52.0	52.0	48.8	45.8	25.5	100 ± 15
31.25	10.5	61.9	59.9	49.4	49.4	46.9	43.9	25.0	100 ± 15
62.5	15.1	57.4	55.4	40.3	40.3	40.9	37.9	23.5	100 ± 15

100	19.3	54.3	52.3	33.0	33.0	36.8	33.8	22.5	100 ± 15
155	24.5	51.4	49.4	24.9	24.9	33.0	30.0	21.6	100 ± 22
200	28.2	49.8	47.8	19.6	19.6	30.8	27.8	21.0	100 ± 22
250	31.8	48.3	46.3	14.5	14.5	28.8	25.8	20.5	100 ± 32
300	35.2	47.1	45.1	9.9	9.9	27.3	24.3	20.1	100 ± 32
350	38.4	46.1	44.1	5.7	5.7	25.9	22.9	19.8	100 ± 32
400	41.5	45.3	43.3	1.8	1.8	24.8	21.8	19.5	100 ± 32
450	44.3	44.5	42.5			23.7	20.7	19.2	100 ± 32
500	47.1	43.8	41.8			22.8	19.8	19.0	100 ± 32
550	49.7	43.2	41.2			22.0	19.0	18.8	100 ± 32
600	52.3	42.6	40.6			21.2	18.2	18.7	100 ± 32
650	54.8	42.1	40.1			20.5	17.5	18.5	100 ± 32

Voltage

UL Voltage Rating
300 V (CMP), 300 V (CL3P)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation	Storage
90°C	-20°C To +75°C	0°C To +50°C	-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
1.0 in (25 mm)	2.5 in (64 mm)

Max. Pull Tension:	25 lbs (11 kg)
Bulk Cable Weight:	28 lbs/1000ft (42 kg/km)

Standards and Compliance

Environmental Suitability:	Plenum, Indoor
Sustainability:	Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum), FT6, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CMP, CMP-LP (0.6A), CL3P-LP (0.6A)
CEC / C(UL) Compliance:	CMP
ICEA Compliance:	S-116-732
IEEE Compliance:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
NEMA Compliance:	ANSI/NEMA WC-66
Data Category:	Category 6
TIA/EIA Compliance:	ANSI/TIA-568.2-D Category 6
Third Party Performance Verification:	Category 6
ISO/IEC Compliance:	ISO/IEC 11801-1, IEC 61156-5
CENELEC Compliance:	Segregation class according EN50174-2 = a
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2020-01-16
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Values above 400 MHz are for Engineering Information Only. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	--

History

Update and Revision:	Revision Number: 0.5 Revision Date: 07-14-2026
----------------------	--

Part Numbers

Variants

Item #	Color	Length	UPC
--------	-------	--------	-----

M57193RB			799936140781
M57193B	Blue, Light	1,000 ft	799936110302
M57196B	Gray	1,000 ft	799936111576
M57197B	Green, Dark	1,000 ft	
M57199B	Orange	1,000 ft	
M57194B	Pink	1,000 ft	
M57198B	Red	1,000 ft	
M57201B	Violet	1,000 ft	
M56905B	White	1,000 ft	799936111545
M57195B	Yellow	1,000 ft	799936111569

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.